



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: STRIKER

7 outlet, 6-ft cord, 1080 joule strip - Protect It! Surge Suppressor



Highlights

- 7 outlets/6-ft. cord
- 1080 joule surge suppression rating
- \$20,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

Description

Tripp Lite's STRIKER offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. AC surge suppression shields connected equipment from damage and performance problems due to transient surges. STRIKER offers 7 AC outlets, 6-ft. cord and diagnostic LEDs to warn of wiring problems and suppressor damage. AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive gray housing with keyhole mounting tabs and 1 designated transformer plug outlet offer convenient protection of desktop computer equipment and accessories. \$20,000 [Ultimate Lifetime Insurance](#) (USA & Canada only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 x NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer-spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/1080 joules/400V UL1449 Let-through Rating

Applications

- Ideal for any desktop, network or home computing application requiring AC line surge protection.

Package Includes

- STRIKER Surge Suppressor
- Instruction manual with warranty information

Features

- 7 outlets
- 6-ft. cord
- Surge suppression rating: 1080 joules
- EMI/RFI noise filtering
- Can accommodate 1 transformer without blocking remaining outlets
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting
- \$20,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only) covers connected equipment

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Supports 1 large transformer plug accessory without covering remaining outlets; accepts up to 4 transformers total
Outlet orientation	Single row
INPUT	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (ft.)	6
Input cord length (m)	1.83
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	72000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	1080
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	400V
EMI / RFI filtering	Up to 20 dB
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping weight (lbs)	1.30

Shipping weight (kg)	0.59
Unit Dimensions (HWD/in)	1.32 x 2.05 x 11.69
Unit Dimensions (HWD/cm)	3.35 x 5.21 x 29.69
Shipping Dimensions (HWD/in)	13.78 x 4.52 x 1.77
Shipping Dimensions (HWD/cm)	35.00 x 11.48 x 4.50
Unit weight (lbs)	1.17
Unit weight (kg)	0.53
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
AC line cord color	Gray
Style	Strip
Outlets center to center measurement	Distance between standard outlets = 29mm; Distance between last standard outlet and transformer outlet = 33mm
Keyhole slot center to center measurement	Distance between slots = 151mm; Distance between slot height = 24mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
NOM (Mexico)	NOM
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=133.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.