


3 Breaker Maintenance Bypass Panel for Select 20 and 30kVA UPS systems

MODEL NUMBER: **SU2030KMBP**



Highlights

- Wall-mount manual bypass panel isolates UPS from connected loads for maintenance with no loss of network availability
- Mechanical interlock system enhances system reliability
- Minimizes sequencing errors
- 3 built-in CH Type circuit breakers
- Compatible with select 20 and 30kVA 3 phase UPS systems

Description

Wall-mount three-breaker manual bypass panel with mechanical interlock system isolates the UPS from connected loads for maintenance with no loss of network availability. 100A breaker with KAIC rating of 10. Compatible with SU20K3/3, SU20K3/3XR5, SU30K3/3 and SU30K3/3XR5.

Features

- Wallmount 3 breaker manual bypass panel with mechanical interlock system
- Isolates the UPS from connected loads for maintenance with no loss of network availability
- 100A breaker with KAIC rating of 10
- Compatible with SU20K3/3, SU20K3/3XR5, SU30K3/3, SU30K3/3XR5 and SV20K__ models.

Specifications

OVERVIEW	
UPC Code	037332181800
Accessory Type	Bypass Panel
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage Description	208Y/120 VAC 3 phase, 4 wire, Ground
OUTPUT	
Output Capacity Details	100A maximum per phase
PHYSICAL	



Powering Business Worldwide



Form Factors Supported	Wallmount
Shipping Dimensions (hwd / in.)	7.50 x 14.50 x 26.50
Shipping Dimensions (hwd / cm)	19.05 x 36.83 x 67.31
Shipping Weight (lbs.)	33.50
Shipping Weight (kg)	15.20
Unit Dimensions (hwd / in.)	12.000 x 24.000 x 5.560
Unit Dimensions (hwd / cm)	30.5 x 61 x 11.7
Unit Weight (lbs.)	27.5
Unit Weight (kg)	12.47
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.