

# 3 Breaker Maintenance Bypass Panel for 40kVA SV40K and SU40K UPS models

MODEL NUMBER: **SU40KMBPK**



### Highlights

- wall-mount manual bypass panel isolates UPS from connected loads for maintenance with no loss of network availability
- Includes Kirk-Key interlock system enhances system reliability
- 3 built-in circuit breakers, heavy duty buswork
- Compatible with select 3 phase UPS systems

### Description

Wall-mount three-breaker manual bypass panel with Kirk-Key interlock system isolates the UPS from connected loads for maintenance with no loss of network availability. 150A breaker with KAIC rating of 65. Key included. Compatible with SU40K.

### Features

- Wallmount 3 breaker manual bypass panel with Kirk Key interlock system
- Isolates the UPS from connected loads for maintenance with no loss of network availability
- 150A breaker with KAIC rating of 65
- Key included
- Compatible with SU40K, and SV40K\_\_ models.

## Specifications

OVERVIEW	
UPC Code	037332146274
Accessory Type	Bypass Panel
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	240V AC
Voltage Compatibility (VAC)	240
PHYSICAL	
Form Factors Supported	Wallmount



Powering Business Worldwide



Shipping Dimensions (hwd / in.)	30.00 x 13.00 x 43.00
Shipping Dimensions (hwd / cm)	76.20 x 33.02 x 109.22
Shipping Weight (lbs.)	225.00
Shipping Weight (kg)	102.06
Unit Dimensions (hwd / in.)	42.360 x 30.120 x 11.750
Unit Dimensions (hwd / cm)	107.6 x 76.5 x 29.8
Unit Weight (lbs.)	220
Unit Weight (kg)	99.79
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.