

# SUPDM56HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: SUPDM56HW



## Description

The SUPDM56HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U and SU6000RT4U) to a totally hardwired solution. Easy quick-connect terminal block allows installation of hardwire distribution module in minutes. Can accept input voltages of 120/208 or 120/240 VAC split-phase power. Detachable hardwire module allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections.

## Features

- The SUPDM56HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U and SU6000RT4U) to a totally hardwired solution
- Easy quick-connect terminal block allows installation of hardwire distribution module in minutes
- Can accept input voltages of 120/208 or 120/240 VAC split-phase power
- Detachable hardwire module allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections

## Specifications

OVERVIEW	
UPC Code	037332126696
Accessory Type	PDU Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 140V AC

## Highlights

- Converts compatible SmartOnline Hot-Swappable Modular UPS systems to hardwire input and output
- For use with input voltages of 120/208 or 120/240 VAC split-phase power
- Convenient quick-disconnect terminal block allows installation in minutes

## System Requirements

- Use with SU5000RT4U and SU6000RT4U split-phase SmartOnline Hot-Swappable Modular UPS Systems

## Package Includes

- SUPDM56HW hardwire PDU
- Mounting Hardware
- Owner's Manual



Powering Business Worldwide



Input Connection Type	Split-phase hardwire (4-wire)
Voltage Compatibility (VAC)	100-140
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	Hardwire
Output Nominal Voltage	120/208, 120/240
<b>PHYSICAL</b>	
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	5.75 x 12.00 x 10.00
Shipping Dimensions (hwd / cm)	14.60 x 30.48 x 25.40
Shipping Weight (lbs.)	4.00
Shipping Weight (kg)	1.81
Unit Dimensions (hwd / in.)	6.000 x 8.250 x 3.250
Unit Dimensions (hwd / cm)	15.24 x 21 x 8.3
Unit Weight (lbs.)	2.75
Unit Weight (kg)	1.25
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.