

SUPDMB568HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: **SUPDMB568HW**



Description

The SUPDMB568HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U, SU6000RT4U, and SU8000RT4U) to a totally hardwired solution. Easy quick-connect terminal block allows installation of hardwire distribution module in minutes. Can accept input voltages of 120/208 or 120/240 VAC split-phase power. Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections.

Features

- Converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU5000RT4U, SU6000RT4U, and SU8000RT4U) to a totally hardwired solution
- Easy quick-connect terminal block allows installation of hardwire distribution module in minutes
- Can accept input voltages of 120/208 or 120/240 VAC split-phase power
- Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections

Highlights

- Converts compatible SmartOnline Hot-Swappable Modular UPS systems to hardwire input and output
- For use with input voltages of 120/208 or 120/240 VAC split-phase power
- Convenient quick-disconnect terminal block allows installation in minutes
- Manual bypass switch eliminates equipment downtime

System Requirements

- Use with SU5000RT4U, SU6000RT4U, and SU8000RT4U split-phase SmartOnline Hot-Swappable Modular UPS Systems

Package Includes

- SUPDMB568HW hardwire PDU
- Mounting Hardware
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332144072
Accessory Type	PDU Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 140V AC
Input Connection Type	Split-phase hardwire (4-wire)
Voltage Compatibility (VAC)	100-140



Powering Business Worldwide



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	Hardwire
Output Nominal Voltage	120/208, 120/240
PHYSICAL	
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	8.90 x 9.40 x 19.50
Shipping Dimensions (hwd / cm)	22.61 x 23.88 x 49.53
Shipping Weight (lbs.)	8.80
Shipping Weight (kg)	3.99
Unit Dimensions (hwd / in.)	6.000 x 17.500 x 6.750
Unit Dimensions (hwd / cm)	15.24 x 44.45 x 17.1
Unit Weight (lbs.)	11.7
Unit Weight (kg)	5.31
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.