



SUPDMB710HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: SUPDMB710HW







Description

The SUPDMB710HW hardwire input/output PDU module converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU10000RT3U and SU8000RT3U) to a totally hardwired solution. Easy quick-connect terminal block allows installation of hardwire distribution module in minutes. Can accept input voltages of 208 or 240 VAC single phase power. Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections.

Features

- Converts compatible SmartOnline Hot-Swappable Modular UPS Systems (models SU10000RT3U and SU8000RT3U) to a totally hardwired solution
- Easy quick-connect terminal block allows installation of hardwire distribution module in minutes
- Can accept input voltages of 208 or 240 VAC single phase power
- Detachable hardwire module with manual bypass switch allows for effortless UPS maintenance without the need to power down connected loads and re-wire input/output connections

Highlights

- Converts compatible SmartOnline Hot-Swappable Modular UPS systems to hardwire input and output
- For use with SU10000RT3U and SU8000RT3U UPS Systems
- Easy quick-connect terminal block installation
- Manual bypass switch supports hot-swap UPS power module replacement

System Requirements

 Use with SU10000RT3U and SU8000RT3U SmartOnline Hot-Swappable Modular UPS Systems

Package Includes

- Hardwire PDU with Bypass Switch
- Mounting Hardware
- Owner's Manual

Specifications

OVERVIEW		
UPC Code	037332136237	
Accessory Type	PDU Module	
Accessory Class	UPS Accessories	
INPUT		
Nominal Input Voltage(s) Supported	208V AC; 240V AC	
Input Connection Type	Hardwire	
Voltage Compatibility (VAC)	208; 240	





OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	Hardwire	
Output Nominal Voltage	208/240V	
PHYSICAL		
Material of Construction	Steel	
Shipping Dimensions (hwd / in.)	10.60 x 7.80 x 9.10	
Shipping Dimensions (hwd / cm)	26.92 x 19.81 x 23.11	
Shipping Weight (lbs.)	9.80	
Shipping Weight (kg)	4.45	
Unit Dimensions (hwd / in.)	5.250 x 7.500 x 6.500	
Unit Dimensions (hwd / cm)	13.3 x 19.1 x 16.5	
Unit Weight (lbs.)	4.6	
Unit Weight (kg)	2.09	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Certifications	CSA (Canada); UL 1778	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	2-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.