



Detachable PDU option with IEC output connections for compatible SmartOnline UPS Systems

MODEL NUMBER: SUPDMB710IEC



Description

The SUPDMB710IEC converts the output of our SmartOnline SU8000RT3U and SU10000RT3U to worldwide output connections. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input/ 6 IEC320 C19 output connections.

Features

- Converts the output of our SmartOnline SU8000RT3U and SU10000RT3U to worldwide output connections
- Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs
- Can accept input voltages of 200-240 VAC
- Hardwire input/ 6 IEC320 C19 output connections

Specifications

OVERVIEW		
UPC Code	037332143594	
Accessory Type	PDU Module	
Accessory Class	UPS Accessories	
INPUT		
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC	
Input Connection Type	Hardwire	
Voltage Compatibility (VAC)	200; 208; 220; 230; 240	

Highlights

- Converts compatible SmartOnline high-voltage UPS systems to provide worldwide compatible output connections
- For use with input voltages of 200-240 VAC
- Hardwired input/ 6 IEC320 C19 output connections
- Manual bypass feature ensures maximum equipment availability

System Requirements

 For use with SmartOnline SU8000RT3U and SU10000RT3U Rack/Tower UPS systems in applications requiring a detachable PDU with manual bypass

Package Includes

- SUPDMB710IEC detachable
 PDU
- Mounting hardware
- Owner's Manual with warranty instructions





OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(6) C19	
Output Nominal Voltage	200/208/220/230/240 VAC	
Overload Protection	6 double-pole 20A circuit breakers	
PHYSICAL		
Material of Construction	Metal	
Shipping Dimensions (hwd / in.)	13.40 x 9.40 x 9.60	
Shipping Dimensions (hwd / cm)	34.04 x 23.88 x 24.38	
Shipping Weight (lbs.)	9.90	
Shipping Weight (kg)	4.49	
Unit Dimensions (hwd / in.)	10.250 x 7.500 x 6.500	
Unit Dimensions (hwd / cm)	26 x 19.1 x 16.5	
Unit Weight (lbs.)	7.9	
Unit Weight (kg)	3.58	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Certifications	CSA (Canada); UL 1778	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	2-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.