

Protect It! Surge Suppressor - 5 Schuko outlets

MODEL NUMBER: SUPER5DEU



Highlights

- 5 Schuko outlets
- 3 m power cord with German/French plug
- 1050 joule rating
- On/off switch with integrated circuit breaker
- Internal safety covers
- Lifetime warranty

Package Includes

- SUPER5DEU AC surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It! SUPER5DEU offers economical AC surge suppression for full protection of 220-250V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. The SUPER5DEU offers 5 Schuko outlets and a 3 meter AC line cord with German/French plug. AC suppression rated at 1050 joules shields equipment from surges and line noise. An on/off switch with integrated circuit breaker provides power control over connected equipment. Internal safety covers protect against accidental contact with unused outlets. Attractive light gray high-impact housing. Lifetime warranty.

INPUT: 3 m AC line cord with German/French plug

OUTPUT: 5 Schuko receptacles

ELECTRICAL: 220-250V AC, 50/60Hz, 10A

FORMAT: Corded multi-outlet strip

SUPPRESSION: - AC: 1050 joules

Features

- Protect It! SUPER5DEU offers economical AC surge suppression
- 1050 joules AC surge suppression shields equipment from surges and line noise
- 5 Schuko outlets protect computers and peripherals
- 3 m AC line cord with German/French plug
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Attractive light gray high-impact housing with keyhole mounting tabs allow versatile placement options
- Internal safety covers protect against accidental contact with unused outlets
- Lifetime warranty

Specifications

OVERVIEW

UPC Code

037332010674



Powering Business Worldwide



INPUT	
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	German; French
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	10
Overload Protection	10A resettable illuminated combo switch/circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1050
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Light Gray
Material of Construction	Plastic
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	16.50 x 4.50 x 2.50



Powering Business Worldwide



Shipping Dimensions (hwd / cm)	41.91 x 11.43 x 6.35
Shipping Weight (lbs.)	1.28
Shipping Weight (kg)	0.58
Unit Dimensions (hwd / in.)	1.750 x 2.000 x 13.250
Unit Dimensions (hwd / cm)	33.67 x 5.08 x 4.45
Unit Weight (lbs.)	0.60
Unit Weight (kg)	0.27
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.