



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SUPER7

Protect It! Surge Suppressor



Highlights

- 7 outlets/7 ft. cord
- 2350 joule rating
- \$75,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

The SUPER7 Surge Suppressor from Tripp Lite has 7 outlets, a 7-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2350 joules to handle the strongest surges. \$75,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

Applications

- Personal computers, CAD/CAM/CAE workstations, network nodes, file servers, point-of-sale terminals, audio/visual devices, and more.

Package Includes

- Super 7 Surge Suppressor
- Instruction manual with warranty information

Features

- 7 outlets
- 7-ft. cord with space-saving right-angle plug
- Surge suppression rating: 2350 joules
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$75,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only) covers connected equipment
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting
- Lifetime product warranty

Specifications

OVERVIEW	
Intended Application	Home/Office
SYSTEM OVERVIEW	
Voltage compatibility	120 VAC
OUTPUT	

Frequency compatibility	50 / 60 Hz
Output watts	1800
Output volt amp capacity (amps)	15
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 5 transformers total
Outlet orientation	Single row of 5, plus 2 side mounted outlets
INPUT	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (ft.)	7 ft.
Input cord length (m)	2.1
Input cord gauge, type	14 gauge, SJT
LEDS ALARMS & SWITCHES	
Switches	Two position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	2350 joules
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150V
UL1499 let through rating	330V - UL Verified
EMI / RFI filtering	Up to 20 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping weight (lbs)	1.6
Shipping weight (kg)	0.7
Unit Dimensions (HWD/in)	10.25 x 2.75 x 1.5
Unit Dimensions (HWD/cm)	26 x 7 x 3.8
Shipping Dimensions (HWD/in)	13 x 5.25 x 1.9

Shipping Dimensions (HWD/cm)	33 x 13.3 x 4.8
Unit weight (lbs)	1.4
Unit weight (kg)	0.6
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
AC line cord color	Gray
Style	Strip
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 1998 Rev. (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Standard warranty period	Lifetime
Connected equipment insurance (USA, Canada, Puerto Rico)	\$75,000

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=131.