



# Protect It! 6-Outlet Surge Protector, 6 ft. (1.83 m) cord, 1340 Joules, Diagnostic LED

MODEL NUMBER: TLM606HJ











## **Highlights**

- 6 outlets / 6-ft. (1.83 m) cord
- 1340 joule rating

#### **Package Includes**

- TLM606HJ surge suppressor
- Instruction manual and warranty information

## **Description**

The TLM606HJ surge suppressor offers complete AC surge suppression for comprehensive protection of personal computers, home stereos, televisions, VCRs, DVD players, power tools and other electrical and electronic equipment. Heavy-duty AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLM606HJ offers six total outlets, a six-foot (1.8-meter) power cord and diagnostic LED to warn of suppressor damage. AC surge suppression rated at 1340 joules shields equipment from surges and line noise. Rugged metal housing offers convenient protection of desktop computer equipment and accessories.

#### **Features**

- 6 outlets
- 6-ft. (1.83 m) cord
- Surge suppression rating: 1340 joules
- EMI/RFI noise filtering
- Diagnostic LED confirms suppressor "protection present" (green)
- Convenient keyhole slots allow secure mounting on wall or desk
- Can accommodate up to 1 transformers without blocking adjacent outlets
- Rugged metal case provides extra safety and durability
- Illuminated on/off switch with integrated 15 amp circuit breaker
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
  equipment damage and indicating replacement is required

# **Specifications**

OVERVIEW	
UPC Code	037332135698





Recommended Electrical Service 1 Input Cord Gauge Type 1 Input Cord Gauge (AWG) 1	120V AC 120V (110-125V) 14 gauge; SJT 14	
Input Cord Gauge Type 1 Input Cord Gauge (AWG) 1	14 gauge; SJT 14	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
voltago compatibility (vito)	120	
Maximum Surge Amps 6	60000	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	6	
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility 5	50 / 60 Hz	
Output Receptacles (	(6) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation (	(2) Yes	
Outlet Orientation	Single row of outlets	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches I	Illuminated on/off switch with integrated 15 amp circuit breaker	
Diagnostic LED Details E	Built-in LED confirms suppressor "protection present" (green) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1340	
AC Suppression Response Time	< 1 ns	
Protection Modes I	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
UL1449 Let Through Rating	400V	
EMI / RFI Filtering	Up to 20 dB	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
	No	





Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Material of Construction	Metal, Plastic	
Power Cord Color	Light Gray	
Form Factors Supported	Supports floor / wall / desktop placement	
Housing Color	Light Gray	
Mounting Holes or Slots	Yes	
Outlets Measurement (Center to Center)	38.89mm	
Receptacle Color	Light gray	
Shipping Dimensions (hwd / in.)	1.50 x 4.30 x 14.30	
Shipping Dimensions (hwd / cm)	3.81 x 10.92 x 36.32	
Shipping Weight (lbs.)	1.50	
Shipping Weight (kg)	0.68	
Unit Dimensions (hwd / in.)	1.500 x 12.500 x 2.500	
Unit Dimensions (hwd / cm)	3.8 x 31.8 x 6.3	
Unit Weight (lbs.)	1.4	
Unit Weight (kg)	0.64	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.