



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLM609GF

Safety Power Strip - Rugged, Safe Power Distribution for Industrial/Automotive/Factory Environments



Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 9 ft. cord with GFCI plug
- Cord wrap with hang holes
- Rugged metal case
- Lifetime limited warranty

Description

This Tripp Lite power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. 6 outlets distribute AC power to a wide range of power tools, drill presses, air compressors, power sanders and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 9 ft. grounded cord with integrated cord clip reaches distant outlets. A GFCI plug protects users from electrical shock in wet or humid environments. A lighted on/off switch provides power control over connected equipment. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Lifetime limited warranty. Its bright yellow color alerts you and others that power cords and tools are in use.

Applications

- Industrial
- Automotive
- Factory
- Hardware

Package Includes

- TLM609GF Safety Power Strip
- 4 safety covers
- Owner's manual

Features

- 6 outlets distribute AC power to a wide range of band saws, drill presses, air compressors, power sanders and more.
- Convenient transformer outlets accommodate multiple transformers without blocking other outlets.
- A 9 ft. grounded cord with integrated cord clip reaches distant outlets.
- A GFCI plug protects users from electrical shock in wet or humid environments.
- A lighted on/off switch provides power control over connected equipment.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Built-in cord wrap with hang holes provides convenient cord management.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting.

- Lifetime limited warranty.
 - Its bright yellow color alerts you and others that power cords and tools are in use.
 - OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury.
- This Tripp Lite product complies with those guidelines.

Specifications

SYSTEM OVERVIEW	
Voltage compatibility	120V AC
OUTPUT	
Frequency compatibility	60 Hz
Output volt amp capacity (amps)	15
Overload protection	GFCI plug
Outlet quantity / type	6 NEMA 5-15R
Transformer accommodation	Yes (2)
Outlet safety covers	Yes (4)
Outlet orientation	Single row
INPUT	
Recommended Electrical Service	120V, 15A
Input connection type	GFCI 5-15P
Input plug features	Integrated cord clip plus GFCI breaker
Input cord length (ft.)	9 ft.
Input cord gauge, type	14 gauge, SJT
LEDS ALARMS & SWITCHES	
Switches	Lighted on/off power switch
PHYSICAL	
Shipping weight (lbs)	3.33
Unit Dimensions (HWD/in)	15.97 x 3.07 x 1.61
Shipping Dimensions (HWD/in)	16.17 x 7.10 x 2.7
Unit weight (lbs)	3.24
Material of construction	All-metal
Integrated keyhole mounting tabs	Yes
Receptacle Color	black
AC line cord color	yellow
CERTIFICATIONS	
Approvals	cULus, RoHS
WARRANTY	

Standard warranty period	Lifetime
---------------------------------	----------

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3675.

© 2009 Tripp Lite. All Rights Reserved.