



Power It! Power Strip with 6 Right-Angle Outlets, 15 ft. (4.57 m) Cord, Transparent Switch Cover

MODEL NUMBER: TLM615NCRA



Highlights

- 6 right-angle outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 15-ft. (4.57 m) power cord
- Rugged metal case
- Keyhole mounting slots

Package Includes

- TLM615NCRA power strip
- · Warranty information
- Instruction manual

Description

The Power It!® TLM615NCRA power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes six right-angle NEMA 5-15R outlets, 15-foot (4.6-meter) AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 15A integrated circuit breaker to prevent dangerous overloads.

Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 6 right-angle NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots provide secure mounting options for a wide variety of surfaces and applications
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 15-ft. (4.57 m) AC power cord
- Rugged metal case provides extra safety and durability
- UL certification

Specifications

OVERVIEW	
UPC Code	037332135681
INPUT	





Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	15A 120V	
Input Cord Gauge Type	14 gauge; SJT	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	15	
Right-Angle Plug	No	
Input Cord Length (m)	4.57	
Integrated Cord Clip	No	
ОИТРИТ		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Overload Protection	15A circuit breaker	
Transformer Accommodation	(3) Yes	
Outlet Orientation	Single row of 6 (right-angle)	
Right-Angle Outlets	Yes	
USER INTERFACE, ALERTS & CON	ITROLS	
Switches	Lighted 2 position switch controls power to all outlets	
Locking Switch Cover	Transparent switch cover snaps tight to prevent accidental shutoff	
PHYSICAL		
Color	Light Gray	
Material of Construction	Metal	
Power Cord Color	Light Gray	
Housing Color	Light Gray	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	Distance between mounting tabs = 203.20mm; Distance between end tabs = 330.17mm	
Outlets Measurement (Center to Center)	1.62 in.	
Receptacle Color	Light gray	
Shipping Dimensions (hwd / in.)	15.50 x 2.40 x 6.50	
Shipping Dimensions (hwd / cm)	39.37 x 6.10 x 16.51	
Shipping Weight (lbs.)	3.00	
Shipping Weight (kg)	1.36	
	1	





Unit Dimensions (hwd / in.)	2.000 x 13.750 x 2.500	
Unit Dimensions (hwd / cm)	35 x 6.35 x 5.1	
Unit Weight (lbs.)	2.8	
Unit Weight (kg)	1.27	
Mounting Details	Includes flanges	
FEATURES & SPECIFICATIONS		
Antimicrobial	No	
Built-In Circuit Breaker	Yes	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks

are the property of their respective owners.