

Power It! 6-Outlet Safety Power Strip, 6 ft. (1.83 m) Cord & Clip, Safety Covers

MODEL NUMBER: TLM626NS



Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 6-ft. (1.83 m) cord
- Rugged metal case

Package Includes

- TLM626NS Safety Power Strip
- 4 safety covers
- Owner's manual

Description

This power strip safely distributes power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. Six outlets distribute AC power to a wide range of power tools, pumps, air compressors and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A six-foot (1.8-meter) grounded cord with integrated cord clip reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. Four safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Its bright yellow color alerts you and others that power cords and tools are in use.

Features

- 6 outlets distribute AC power to a wide range of power tools, pumps, air compressors and more.
- Convenient transformer outlets
- A 6-ft. (1.83 m) grounded cord with integrated cord clip reaches distant outlets.
- A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting
- Its bright yellow color alerts you and others that power cords and tools are in use.
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This product complies with those guidelines.

Specifications

OVERVIEW	
UPC Code	037332140173



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	Combo power switch and circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row
Right-Angle Outlets	Yes
Outlet Safety Covers Detail	Includes 4 outlet safety covers
PHYSICAL	
Color	Yellow; Black
Material of Construction	Metal
Power Cord Color	Yellow
Housing Color	Yellow; Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	225mm
Outlets Measurement (Center to Center)	Distance between standard outlets = 1.19 in.; Distance between standard and transformer outlets = 1.77 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	13.70 x 2.00 x 4.70
Shipping Dimensions (hwd / cm)	34.80 x 5.08 x 11.94
Shipping Weight (lbs.)	1.74
Shipping Weight (kg)	0.79
Unit Dimensions (hwd / in.)	12.230 x 2.300 x 1.280



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Dimensions (hwd / cm)	31.06 x 5.84 x 3.25
Unit Weight (lbs.)	1.34
Unit Weight (kg)	0.61
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.