



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TLM626NS

### Safety Power Strip - Rugged, Safe Power Distribution for Industrial/Automotive/Factory Environments



#### Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 6 ft. cord
- Rugged metal case
- Lifetime limited warranty

#### Description

This Tripp Lite power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. 6 outlets distribute AC power to a wide range of power tools, pumps, air compressors and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 6 ft. grounded cord with integrated cord clip reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Lifetime limited warranty. Its bright yellow color alerts you and others that power cords and tools are in use.

#### Applications

- Industrial
- Automotive
- Factory
- Hardware

#### Package Includes

- TLM626NS Safety Power Strip
- 4 safety covers
- Owner's manual

#### Features

- 6 outlets distribute AC power to a wide range of power tools, pumps, air compressors and more.
- Convenient transformer outlets
- A 6 ft. grounded cord with integrated cord clip reaches distant outlets.
- A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting
- Lifetime limited warranty

- Its bright yellow color alerts you and others that power cords and tools are in use.
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.

## Specifications

SYSTEM OVERVIEW	
Voltage compatibility	120V AC
OUTPUT	
Frequency compatibility	60 Hz
Output volt amp capacity (amps)	15
Overload protection	Combo power switch and circuit breaker
Outlet quantity / type	6 NEMA 5-15R
Transformer accommodation	Yes (2)
Outlet safety covers	Yes (4)
Outlet orientation	Single row
INPUT	
Recommended Electrical Service	120V, 15A
Input connection type	NEMA 5-15P
Input plug features	Integrated cord clip
Input cord length (ft.)	6 ft.
Input cord gauge, type	14 gauge, SJT
PHYSICAL	
Shipping weight (lbs)	1.58
Unit Dimensions (HWD/in)	12.23 x 2.30 x 1.28
Shipping Dimensions (HWD/in)	13.61 x 4.97 x 2.01
Unit weight (lbs)	1.34
Material of construction	All-metal
Integrated keyhole mounting tabs	Yes
Receptacle Color	black
AC line cord color	yellow
CERTIFICATIONS	
Approvals	cULus, RoHS
WARRANTY	
Standard warranty period	Lifetime

---

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3680](http://www.tripplite.com/en/products/model.cfm?txtModelID=3680).

---

© 2010 Tripp Lite. All Rights Reserved.