



Protect It! 6-Outlet Industrial Safety Surge Protector, 6 ft. Cord, 900 Joules, Outlet Covers

MODEL NUMBER: TLM626SA



Description

This surge suppressor is designed to provide safe, reliable surge protection in harsh environments. A 900joule rating can protect connected equipment against even the strongest surges. Six outlets protect connected equipment against damaging surges, spikes and line noise. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A six-foot (1.8-meter) grounded cord reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. Protected LED confirms that connected equipment is being protected. Four safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. As an added safety feature, the surge suppressor's bright yellow color alerts you and others that power cords and tools are in use.

Features

- 6 outlets protect connected equipment against damaging surges, spikes and line noise
- 6 ft. grounded cord reaches distant outlets
- Lighted ON/OFF switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload.
- Protected LED If this green LED ever goes out, we will replace your surge suppressor under warranty at no charge!
- Convenient transformer outlets accommodate multiple transformers without blocking other outlets.
- 4 safety covers shield unused outlets from debris and accidental contact.
- Rugged metal case stands up to the harshest environments.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting.
- 900 joules of surge protection
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This product complies with those guidelines.
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
 equipment damage and indicating replacement is required

Specifications

Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 6 ft. cord
- 900 joule rating
- Rugged metal case

Package Includes

- TLM626SA Safety Surge Suppressor
- 4 safety covers
- Owner's manual





OVERVIEW		
UPC Code	037332140104	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	45000	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	6	
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	60 Hz	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Overload Protection	Combo power switch and circuit breaker	
Transformer Accommodation	(4) Yes	
Outlet Orientation	1 single row of 6	
Right-Angle Outlets	Yes	
Outlet Safety Covers Detail	Includes 4 outlet safety covers	
USER INTERFACE, ALERTS & CON	TROLS	
Diagnostic LED(s)	Yes	
Switches	Lighted on/off power switch	
Diagnostic LED Details	1 green "protected" LED confirms surge suppression is present	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	900	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
EMI / RFI Filtering	Up to 20 dB	





Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Metal
Power Cord Color	Yellow
Housing Color	Yellow
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	155 mm
Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between transformer and standard outlets = 45mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	7.30 x 13.70 x 5.00
Shipping Dimensions (hwd / cm)	18.54 x 34.80 x 12.70
Shipping Weight (lbs.)	1.70
Shipping Weight (kg)	0.77
Unit Dimensions (hwd / in.)	12.230 x 2.300 x 1.280
Unit Dimensions (hwd / cm)	31.06 x 5.84 x 3.25
Unit Weight (lbs.)	1.46
Unit Weight (kg)	0.66
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.