



Protect It! Surge Protector with 6 Right-Angle Outlets, 15 ft. (4.57 m) Cord, 1340 Joules, Tel/Modem Protection

MODEL NUMBER: TLM626TEL15



Description

The TLM626TEL15 surge suppressor offers complete AC and Tel/DSL line surge suppression for comprehensive protection of workstations, personal computers, home stereos, televisions, VCRs, DVD players and other sensitive electronics. Heavy-grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ-11 telephone line suppression jacks protect a single dialup modem, DSL modem, fax or phone line. TLM626TEL15 offers six right-angle outlets, a 15-foot power cord and diagnostic LEDs to warn of wiring problems and suppressor damage. AC surge suppression rated at 1340 joules shields equipment from surges and line noise. Rugged metal housing with two designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories.

Features

- 6 right-angle outlets
- 15-ft. (4.57 m) cord
- Built-in RJ-11 jacks prevent surges from damaging your telephone/DSL/modem/fax equipment; 6 ft. telephone cord included
- Surge suppression rating: 1340 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker protects against overload
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
- · Convenient keyhole slots allow secure mounting on wall or desk
- Can accommodate up to 2 transformers without blocking adjacent outlets
- Rugged metal case provides extra safety and durability
- Illuminated power switch
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

Highlights

- 6 right-angle outlets / 15-ft. (4.57 m) cord
- 1340 joule rating
- Tel/DSL surge protection (1 line)

Package Includes

- TLM626TEL15 surge suppressor
- 6-ft. (1.83 m) RJ-11 phone cord
- Instruction manual and warranty information





OVERVIEW	
UPC Code	037332128652
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable combo switch / circuit breaker
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row of outlets
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1340
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20 dB





Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Material of Construction	Metal
Power Cord Color	Black
Form Factors Supported	Supports floor / wall / desktop placement
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	225 mm
Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between transformer and standard outlets = 45mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	25.50 x 14.30 x 6.00
Shipping Dimensions (hwd / cm)	64.77 x 36.32 x 15.24
Shipping Weight (lbs.)	2.70
Shipping Weight (kg)	1.22
Unit Dimensions (hwd / in.)	1.500 x 12.250 x 2.250
Unit Dimensions (hwd / cm)	3.81 x 31.12 x 5.72
Unit Weight (lbs.)	1.8
Unit Weight (kg)	0.82
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed
Product Compliance	FCC Part 68; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty





Connected Equipment Insurance (U.S., Canada & Puerto Rico)

\$75,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.