



# Power It! 8-Outlet Safety Power Strip, 25 ft. (7.62 m) Cord with GFCI Plug

MODEL NUMBER: TLM825GF











#### **Highlights**

- 8 outlets (including transformer outlets and 4 safety covers)
- 25-ft. (7.62 m) extra-long cord with GFCI plug
- Cord wrap with hang holes
- · Rugged metal case

#### **Package Includes**

- TLM825GF Safety Power Strip
- · 4 safety covers
- · Owner's manual

## **Description**

This power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. Eight outlets distribute AC power to a wide range of power tools, pumps, machinery, air compressors and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 25-foot (7.6-meter) grounded cord with integrated cord clip reaches distant outlets. A GFCI plug protects users from electrical shock in wet or humid environments. A lighted on/off switch provides power control over connected equipment. Four safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Its bright yellow color alerts you and others that power cords and tools are in use.

## **Features**

- 8 outlets distribute AC power to a wide range of power tools, pumps, machinery, air compressors and more.
- Convenient transformer outlets accommodate multiple transformers without blocking other outlets.
- A 25-ft. (7.62 m) grounded cord with integrated cord clip reaches distant outlets.
- A GFCI plug protects users from electrical shock in wet or humid environments.
- A lighted on/off switch with integrated 15 amp circuit breaker provides power control and overload protection over connected equipment.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Built-in cord wrap with hang holes provides convenient cord management.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting.
- Its bright yellow color alerts you and others that power cords and tools are in use.
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may
  cause minor or moderate injury. This product complies with those guidelines.

# **Specifications**





OVERVIEW		
UPC Code	037332140128	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	15A 120V	
Input Cord Gauge Type	14 gauge; SJT	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	25	
Right-Angle Plug	No	
Input Cord Length (m)	7.62	
Integrated Cord Clip	Yes	
ОИТРИТ		
Frequency Compatibility	60 Hz	
Output Receptacles	(8) 5-15R	
Circuit Breaker (amps)	15	
Overload Protection	GFCI plug	
Transformer Accommodation	(6) Yes	
Outlet Orientation	1 bank of 5, 1 bank of 3 (transformer outlets)	
Right-Angle Outlets	Yes	
Outlet Safety Covers Detail	Includes 4 outlet safety covers	
USER INTERFACE, ALERTS & CONTROLS		
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch	
PHYSICAL		
Color	Yellow; Black	
Material of Construction	Metal	
Power Cord Color	Yellow	
Housing Color	Yellow; Black	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	145mm	
Outlets Measurement (Center to Center)	Distance between standard outlets = 1 in.; Distance between transformer outlets = 2 in.	
Receptacle Color	Black	





Shipping Dimensions (hwd / in.)	2.25 x 11.50 x 13.50	
Shipping Dimensions (hwd / cm)	5.72 x 29.21 x 34.29	
Shipping Weight (lbs.)	5.20	
Shipping Weight (kg)	2.36	
Unit Dimensions (hwd / in.)	10.260 x 5.130 x 1.570	
Unit Dimensions (hwd / cm)	26.06 x 13.03 x 3.99	
Unit Weight (lbs.)	4.63	
Unit Weight (kg)	2.10	
FEATURES & SPECIFICATIONS		
Antimicrobial	No	
Built-In Circuit Breaker	Yes	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.