

## Protect It! 8-Outlet Industrial Safety Surge Protector, 25 ft. Cord, 3900 Joules, Cord Wrap, Hang Holes

MODEL NUMBER: TLM825SA



### Highlights

- 8 outlets (including transformer outlets and 4 safety covers)
- 25 ft. extra-long cord
- 3900 joule rating
- Cord wrap with hang holes
- Rugged metal case

### Package Includes

- TLM825SA Safety Surge Suppressor
- 4 safety covers
- Owner's manual

### Description

This surge suppressor is designed to provide safe, reliable surge protection in harsh environments. A high 3900-joule rating can protect connected equipment against even the strongest surges. Eight outlets protect connected equipment against damaging surges, spikes and line noise. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 25-foot (7.6-meter) grounded cord with integrated cord clip reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. Protected LED confirms that connected equipment is being protected. Four safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. As an added safety feature, the surge suppressor's bright yellow color alerts you and others that power cords and tools are in use.

### Features

- 8 OUTLETS protect connected equipment against damaging surges, spikes and line noise
- 25 ft. GROUNDED CORD with INTEGRATED CORD CLIP reaches distant outlets.
- LIGHTED ON/OFF SWITCH with INTEGRATED CIRCUIT BREAKER provides power control over connected equipment. Breaker protects against dangerous system overload.
- PROTECTED LED - If this green LED ever goes out, we will replace your surge suppressor under warranty at no charge!
- CONVENIENT TRANSFORMER OUTLETS accommodate multiple transformers without blocking other outlets.
- 4 SAFETY COVERS shield unused outlets from debris and accidental contact.
- RUGGED METAL CASE stands up to the harshest environments.
- CORD WRAP with HANG HOLES provides convenient cord management.
- INTEGRATED KEYHOLE SLOTS on bottom panel provide convenient wall/desk mounting.
- 3900 joules of surge protection
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This product complies with those guidelines.
- \$100,000 ULTIMATE LIFETIME INSURANCE (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing

equipment damage and indicating replacement is required

## Specifications

<b>OVERVIEW</b>	
UPC Code	037332140067
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	120000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	25
Right-Angle Plug	No
Input Cord Length (m)	7.62
Integrated Cord Clip	Yes
<b>OUTPUT</b>	
Frequency Compatibility	60 Hz
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Overload Protection	Combo power switch and circuit breaker
Transformer Accommodation	(5) Yes
Outlet Orientation	1 bank of 5, 1 bank of 3 (transformer outlets)
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Lighted on/off power switch
Diagnostic LED Details	1 green "protected" LED confirms surge suppression is present
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	3900
AC Suppression Response Time	< 1 ns



Powering Business Worldwide

TRIPP LITE  
SERIES

Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400 L-N, 400 L-G, 500 N-G
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Metal
Power Cord Color	Yellow
Housing Color	Black; Yellow
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	145 mm
Outlets Measurement (Center to Center)	Distance between standard outlets = 25.40mm; Distance between standard and transformer outlets = 50.80mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	12.50 x 2.40 x 9.00
Shipping Dimensions (hwd / cm)	31.75 x 6.10 x 22.86
Shipping Weight (lbs.)	5.20
Shipping Weight (kg)	2.36
Unit Dimensions (hwd / in.)	10.260 x 5.130 x 1.570
Unit Dimensions (hwd / cm)	26.06 x 13.03 x 3.99
Unit Weight (lbs.)	4.52
Unit Weight (kg)	2.05
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL 1449; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE  
SERIES

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 &nbsp; <a href="https://tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a> &nbsp;
---------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.