



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLP1008TEL

Protect It! Surge Suppressor



Highlights

- 10 outlets / 8-ft. cord
- 2395 joule rating
- 1 in/2 out tel/modem surge protection
- 5 transformer spaces
- \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

Description

Tripp Lite's TLP1008TEL offers economical AC surge suppression for protection of workstations, PCs, telecom systems, home electronics and other sensitive equipment. The TLP1008TEL features 10 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs to warn of suppressor damage. The unit has a surge suppression rating of 2395 joules to shield equipment from line noise and the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

PLUG/OUTLETS: Input: NEMA5-15P/Output: 10 NEMA5-15R/8-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 5 transformer-spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/2395 joules/330V UL1449

Applications

- Ideal for home computers, TV/VCR/DVD players, stereos and other important electrical equipment

Package Includes

- TLP1008TEL surge suppressor
- 6-ft. RJ11 telephone cord
- Instruction manual with warranty information

Features

- 10 outlets with integrated child safety covers
- 8-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment — built-in splitter protects two devices sharing a single line; 6-ft. telephone cord included
- Surge suppression rating: 2395 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status

- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate up to 5 transformers without blocking remaining outlets
- \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only) covers connected equipment
- Keyhole supports for wall mounting
- Failsafe shutdown mode
- Lighted power switch
- Lifetime product warranty

Specifications

| OVERVIEW | |
|---------------------------------|--|
| Intended Application | Home/Office |
| SYSTEM OVERVIEW | |
| Voltage compatibility | 120 V AC |
| OUTPUT | |
| Frequency compatibility | 50 / 60 Hz |
| Output watts | 1800W |
| Output volt amp capacity (amps) | 15A |
| Overload protection | 15A resettable circuit breaker |
| Outlet quantity / type | 10 NEMA 5-15R |
| Transformer accommodation | Supports 5 large transformer plug accessories without covering remaining outlets, accepts up to 8 transformers total |
| Outlet safety covers | Includes built-in sliding outlet safety covers |
| Outlet orientation | Two rows of outlets, including 5 widely spaced for transformers |
| INPUT | |
| Recommended Electrical Service | 120V (110-125V) |
| Input connection type | NEMA 5-15P |
| Input plug features | Space-saving right angle input plug |
| Input cord length (ft.) | 8 ft. |
| Input cord length (m) | 2.4 |
| Input cord gauge, type | 14 gauge, SJT |
| LEDS ALARMS & SWITCHES | |
| Switches | Two-position on/off power switch |
| Diagnostic LEDs | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |
| AC suppression joule rating | 2395 joules |
| AC suppression response time | < 1 ns |
| Protection modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping voltage (RMS) | 150V |

| | |
|--|--|
| UL1499 let through rating | 330V - UL Verified |
| EMI / RFI filtering | Up to 40dB |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | Yes |
| Telephone/DSL Protection Details | 1 line |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Unit Dimensions (HWD/in) | 11.6 x 5 x 1.9 |
| Unit Dimensions (HWD/cm) | 29.5 x 12.7 x 4.8 |
| Shipping Dimensions (HWD/in) | 14.75 x 7.75 x 2 |
| Shipping Dimensions (HWD/cm) | 37.5 x 19.7 x 5.1 |
| Unit weight (lbs) | 1.4 |
| Unit weight (kg) | 0.6 |
| Material of construction | Plastic |
| Integrated keyhole mounting tabs | Keyhole mounting tabs enable wall mounting |
| AC line cord color | Black |
| Style | Strip |
| SPECIAL FEATURES | |
| Right-Angle Plug | Yes |
| CERTIFICATIONS | |
| UL1449 1998 Rev. (AC Suppression) | UL1449 |
| UL1363 (Power Tap) | UL1363 |
| UL497A (Communications) | UL497A |
| FCC Part 68 (Communications) | FCC Part 68 |
| cUL / CSA (Canada) | cUL |
| Industry Canada (Communications) | Industry Canada |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |
| Standard warranty period | Lifetime |
| Connected equipment insurance (USA, Canada, Puerto Rico) | \$150,000 |

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2634.

© 2009 Tripp Lite. All Rights Reserved.