



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TLP1008TEL

### 10 outlet, 8ft cord, 2395 joules, Tel/modem protection - Protect It! Surge Suppressor



#### Highlights

- 10 outlets / 8-ft. cord
- 2395 joule rating
- 1 in/2 out tel/modem surge protection
- 5 transformer spaces
- \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

#### Description

Tripp Lite's TLP1008TEL offers economical AC surge suppression for protection of workstations, PCs, telecom systems, home electronics and other sensitive equipment. The TLP1008TEL features 10 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs to warn of suppressor damage. The unit has a surge suppression rating of 2395 joules to shield equipment from line noise and the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

PLUG/OUTLETS: Input: NEMA5-15P/Output: 10 NEMA5-15R/8-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 5 transformer-spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/2395 joules/400V UL1449 3rd Edition

#### Applications

- Ideal for home computers, TV/VCR/DVD players, stereos and other important electrical equipment

#### Package Includes

- TLP1008TEL surge suppressor
- 6-ft. RJ11 telephone cord
- Instruction manual with warranty information

#### Features

- 10 outlets with integrated child safety covers
- 8-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment — built-in splitter protects two devices sharing a single line; 6-ft. telephone cord included
- Surge suppression rating: 2395 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status

- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate up to 5 transformers without blocking remaining outlets
- \$150,000 [Ultimate Lifetime Insurance](#) (USA & Canada only) covers connected equipment
- Keyhole supports for wall mounting
- Failsafe shutdown mode
- Lighted power switch
- Lifetime product warranty

## Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800W
Circuit Breaker (amps)	15A
Overload protection	15A resettable circuit breaker
Outlet quantity / type	10 NEMA 5-15R
Transformer accommodation	Supports 5 large transformer plug accessories without covering remaining outlets, accepts up to 8 transformers total
Outlet safety covers	Includes built-in sliding outlet safety covers
Outlet orientation	Two rows of outlets, including 5 widely spaced for transformers
INPUT	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	8
Input cord length (m)	2.4
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	120000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and two-position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	2395
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150V

UL1499 let through rating	400V - UL Verified
EMI / RFI filtering	Up to 40dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Unit Dimensions (HWD/in)	12 x 5.25 x 2
Shipping Dimensions (HWD/in)	14 x 7.75 x 2.25
Unit weight (lbs)	2
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
AC line cord color	Black
Style	Strip
Outlets center to center measurement	Between Standard Outlets = 28.4mm; Between Standard and Transformer Outlets = 56.8mm
Keyhole slot center to center measurement	108mm
<b>SPECIAL FEATURES</b>	
Right-Angle Plug	Yes
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (U.S., Canada & Puerto Rico)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 <a href="#">Ultimate Lifetime Insurance</a>

---

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2634](http://www.tripplite.com/en/products/model.cfm?txtModelID=2634).

---

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.