



# Protect It! 10-Outlet Surge Protector, 8 ft. (2.43 m) Cord, 3345 Joules, Tel/Modem/Coaxial Protection

### MODEL NUMBER: TLP1008TELTV



#### Description

The TLP1008TELTV offers economical AC surge suppression for protection of workstations, PCs, telecom systems, home electronics and other sensitive equipment. The TLP1008TLTV features 10 outlets, an eight-foot (2.4 meters) cord with a space-saving right-angle plug, and diagnostic LEDs to warn of suppressor damage. The unit has a surge suppression rating of 3345 joules to shield equipment from line noise and the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. Built-in 2.2 GHz gold coax jacks prevent surges from damaging your cable/satellite equipment.

#### Features

- 10 outlets with child safety covers
- 8-ft. (2.43 m) cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment; built-in splitter protects two devices sharing a single line; 6-ft. (1.83 m) telephone cord included
- Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment; 6-ft gold coax cable included
- Surge suppression rating: 3345 joule protection
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate up to 4 transformers without blocking remaining outlets
- · Keyhole supports for wall mounting
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
- · Lighted power switch

## **Specifications**

#### **Highlights**

- 10 outlets / 8-ft. (2.43 m) cord
- 1 in/2 out tel/modem surge protection
- 1 line 2.2GHz gold coaxial protection
- 3345 joule rating

#### **Package Includes**

- TLP1008TELTV surge suppressor
- 6-ft. RJ11 cable
- 6-ft. (1.83 m) gold coax cable
- Instruction manual and warranty information





OVERVIEW UPC Code	037332119070	
	037332119070	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	135000	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	8	
Right-Angle Plug	Yes	
Input Cord Length (m)	2.44	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(10) 5-15R	
Circuit Breaker (amps)	15	
Overload Protection	15A resettable circuit breaker	
Transformer Accommodation	(8) Yes	
Outlet Orientation	Two rows of outlets, including 4 widely spaced for transformers	
Right-Angle Outlets	No	
Outlet Safety Covers Detail	Includes built-in sliding outlet safety covers	
USER INTERFACE, ALERTS & CON	TROLS	
Diagnostic LED(s)	Yes	
Switches	Two-position on/off power switch	
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	3345	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
UL1449 Let Through Rating	400V - UL Verified	





EMI / RFI Filtering	Up to 40 dB	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection Details	1 line	
Cable (Coax) Protection	Yes	
Cable (Coax) Protection Details	1 line	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	Yes	
PHYSICAL		
Material of Construction	Plastic	
Power Cord Color	Black	
Housing Color	Black	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	108 mm	
Outlets Measurement (Center to Center)	Between Standard Outlets = 28.4mm; Between Standard and Transformer Outlets = 56.8mm	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	14.40 x 2.50 x 8.20	
Shipping Dimensions (hwd / cm)	36.58 x 6.35 x 20.83	
Shipping Weight (lbs.)	2.70	
Shipping Weight (kg)	1.22	
Unit Dimensions (hwd / in.)	11.800 x 5.300 x 1.800	
Unit Dimensions (hwd / cm)	29.5 x 12.7 x 6.5	
Unit Weight (lbs.)	2.2	
Unit Weight (kg)	1.00	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; UL 1449; UL 497A; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		





Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.