

Personal Desktop Charging Station with 2-Outlet Surge Protector, 6 ft. (1.83 m) Cord, 1080 Joules, 4 x USB (4.8A total)

MODEL NUMBER: TLP26USBB



Highlights

- 2 outlet / 6-ft. cord
- 1080 joule rating
- 4.8 amp quad port USB charger

Package Includes

- TLP26USBB Personal Desktop Charging Station
- Instruction manual with warranty information

Description

The TLP26USBB Personal Desktop Charging Station provides exceptional convenience for daily charging tasks. Perfect for home, office, workstations and dorm rooms. With two AC outlets for safe power and four USB ports with 4.8 amps of total power, this charging station can easily handle multiple devices. The built-in slot can hold your tablet or phone for hands-free viewing while charging. The TLP26USBB offers two total outlets, a six-foot power cord, four USB charging ports for a total of 4.8 amps and a diagnostic LED to warn of suppressor damage. AC suppression rated at 1080 joules shields equipment from surges and line noise.

Features

- 2 outlets
- 6-ft. (1.83 m) cord
- 4 USB charging ports - 4.8 amp total
- Built in slot to hold phones and tablets
- Surge suppression rating: 1080 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Green protection LED
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332183385



Powering Business Worldwide



Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	16 gauge; SJT
Input Cord Gauge (AWG)	16; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	15
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
CHARGING	
Number of Charging Ports	4
Total Charging Watts	24
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(4) 4.8A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns

Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	3.60 x 6.50 x 5.80
Shipping Dimensions (hwd / cm)	9.14 x 16.51 x 14.73
Shipping Weight (lbs.)	1.60
Shipping Weight (kg)	0.73
Unit Dimensions (hwd / in.)	1.420 x 5.210 x 5.210
Unit Dimensions (hwd / cm)	3.61 x 13.23 x 13.23
Unit Weight (lbs.)	1.2
Unit Weight (kg)	0.54
Input Cord Color	Black
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide



Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance
---	--

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.