



Protect It! 6-Outlet Surge Protector - 4 Rotating Outlets, 5-15P Input, 1440 Joules, Tel/Modem/Coax Protection, Black

MODEL NUMBER: TLP606RNET











Protects your computer and other home/office electronics against dangerous power surges, spikes and line noise.

Features

6-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home, office, retail or industrial workstation, this Protect It!® surge protector features a surge protection rating of 1440 joules to defend your valuable electronic components against power surges and spikes. The six-foot (1.8-meter) power cord with right-angle NEMA 5-15P plug connects to a wall outlet. Rear mounting slots allow installation of the high-impact plastic housing on a wall or other flat surface.

Connectors and NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, wireless router, desk lamp and other home/office electronics into six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. Two outlets are set apart to accommodate bulky transformers without blocking the other outlets. The other four outlets can rotate to allow easy connection of plugs. Surge-protected gold coaxial connectors and RJ11 Ethernet connectors also protect cable, satellite, antenna, telephone and Internet equipment.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

The on/off button gives you immediate one-touch control over all AC outlets. Two diagnostic LEDs confirm at a glance that your equipment is grounded and protected. An integrated 15A circuit breaker provides overload protection for connected devices. Automatic shutoff permanently cuts power to outlets if the protection circuit is incapacitated, preventing equipment damage and indicating replacement is required.

Specifications

OVERVIEW	
UPC Code	037332178244

Highlights

- 6 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment
- 1440 joules protect your valuable electronics against dangerous surges and spikes
- Easy-to-see LEDs show at a glance that your equipment is protected and grounded
- Automatic shutoff prevents equipment damage if protection circuit is incapacitated
- High-impact plastic housing stands up in demanding home or office environments

Package Includes

- TLP606RNET 6-Outlet Surge Protector, Black
- Gold coaxial cable, 6 ft. (1.8 m)
- Telephone cable, 6 ft.
- Ethernet network cable, 6 ft.
- Owner's manual





INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Plug Features	Right Angle (90D)	
Input Cord Gauge Type	14 gauge; SJT	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	6	
Right-Angle Plug	Yes	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	60 Hz	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(4) Yes	
Outlet Orientation	Rotatable	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Diagnostic LED Details	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1440	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
UL1449 Let Through Rating	400, 500, 500	
EMI / RFI Filtering	150 kHz to 100 mHz	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection Details	1 line	
Cable (Coax) Protection	Yes	





Cable (Coax) Protection Details	1 line	
Network (Ethernet) Protection	Yes	
Telephone/DSL Protection	Yes	
PHYSICAL		
Material of Construction	Plastic	
Power Cord Color	Black	
Housing Color	Black	
Mounting Holes or Slots	No	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	2.00 x 6.10 x 12.90	
Shipping Dimensions (hwd / cm)	5.08 x 15.49 x 32.77	
Shipping Weight (lbs.)	2.30	
Shipping Weight (kg)	1.04	
Unit Dimensions (hwd / in.)	2.200 x 5.910 x 4.720	
Unit Dimensions (hwd / cm)	5.6 x 15 x 12	
Unit Weight (lbs.)	2.22	
Unit Weight (kg)	1.01	
Input Cord Color	Black	
COMMUNICATIONS		
Network Compatibility	100 Mbps (Fast Ethernet)	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	Yes	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 497A; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.