



Protect It! 8-Outlet Surge Protector, 8 ft. (2.43 m) Cord, 2160 Joules, Tel/Fax/Modem/Coax Protection, RJ11

MODEL NUMBER: TLP808TELTV











Highlights

- 8 outlets / 8-ft. (2.43 m) cord
- 2160 joule rating
- 2.2GHz gold coaxial surge protection
- Modem/fax surge protection

Package Includes

- TLP808TELTV
- 6-ft. (1.83 m) telephone cord
- 6-ft. (1.83 m) gold coax cable
- Instruction manual with warranty information

Description

The TLP808TELTV surge suppressor has eight outlets, an eight-foot (2.4 meters) cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. Built-in 2.2 GHz gold coax jacks prevent surges from damaging your cable/satellite equipment.

Features

- 8 outlets with integrated child safety covers; charcoal gray housing
- 8-ft. (2.43 m) cord with space-saving right-angle plug
- Built-in RJ11 jacks (1 in/2 out) prevent surges from damaging your modem/fax/phone equipment; 6-ft. (1.83 m) telephone cord included
- Built-in 2.2GHz gold coax jacks prevent surges from damaging your cable/satellite equipment; 6-ft. (1.83 m) gold coax cable included
- Surge suppression rating: 2160 joules
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Diagnostic LEDs indicate protection present & ground present
- Audible alarm notifies user when the unit is damaged and needs to be replaced
- Keyhole supports for wall mounting
- · Lighted power switch
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
 equipment damage and indicating replacement is required

Specifications

OVERVIEW





UPC Code	037332095343
INDUT	
INPUT	1001/10
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Plug Features	Right Angle (36D)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(6) Yes
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
Right-Angle Outlets	No
Outlet Safety Covers Detail	Includes built-in sliding outlet safety covers
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Audible Alarm	Audible alarm
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2160
AC Suppression Response Time	<1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	330/400/400





	T	
EMI / RFI Filtering	Up to 40 dB	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection Details	1 line	
Cable (Coax) Protection	Yes	
Cable (Coax) Protection Details	1 line	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	Yes	
PHYSICAL		
Material of Construction	Plastic	
Power Cord Color	Gray	
Housing Color	Gray	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	Distance between horizontal tabs = 75 mm; Distance between vertical tabs = 41.6 mm	
Outlets Measurement (Center to Center)	Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm	
Receptacle Color	Gray	
Shipping Dimensions (hwd / in.)	11.50 x 2.40 x 8.70	
Shipping Dimensions (hwd / cm)	29.21 x 6.10 x 22.10	
Shipping Weight (lbs.)	2.40	
Shipping Weight (kg)	1.09	
Unit Dimensions (hwd / in.)	4.860 x 9.550 x 1.510	
Unit Dimensions (hwd / cm)	12.34 x 24.26 x 3.84	
Unit Weight (lbs.)	1.9	
Unit Weight (kg)	0.86	
Input Cord Color	White	
FEATURES & SPECIFICATIONS		
Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line	
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed	
Product Compliance	FCC Part 68; RoHS	





WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.