



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TMC-6

Protect It! Surge Suppressor

Highlights

- 6 outlets / 6-ft. cord
- 1850 joule rating
- Tel/modem surge protection
- Individual switches
- \$50,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)



Description

Tripp Lite's TOUCHMASTER COMPACT surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TOUCHMASTER COMPACT offers 6 total outlets, 6 foot cord and LEDs to warn of power and wiring problems. Heavy grade AC suppression rated at 1850 joules shields equipment from surges and line noise. Attractive, slim design is perfect for use under desktop computer monitors or notebook computers. Individual switches offer power control over connected equipment. Lifetime warranty with \$50,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Slim, compact design perfect for use under desktop monitors and notebook computers

SUPPRESSION: AC: 150V RMS Clamping/1850 joules/330V UL1449

Applications

- Ideal for PCs, notebook computers, peripherals and home electronics

Package Includes

- TOUCHMASTER COMPACT surge suppressor
- 6-ft. phone cord
- Instruction manual and warranty information

Features

- 6 outlets
- 6-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment; 6-ft. telephone cord included
- Surge suppression rating: 1850 joules
- EMI/RFI noise filtering

- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green), "grounded" (red) status and "power on" (green)
- Always on outlet provides power for equipment you always need on — even when the "master" switch is off
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Allows for the computer to be controlled by the "master" switch and other outlets to be controlled either the "master" switch or corresponding switch on the front panel
- \$50,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only) covers connected equipment
- Lifetime product warranty

Specifications

OVERVIEW	
Intended Application	Home/Office
SYSTEM OVERVIEW	
Voltage compatibility	120 V AC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Output volt amp capacity (amps)	15
Outlet quantity / type	6 NEMA 5-15R
INPUT	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P input plug
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	6 ft.
Input cord length (m)	1.8
Input cord gauge, type	14 gauge, SJT
LEDS ALARMS & SWITCHES	
Switches	Includes 5 front panel AC power switches. 4 switches control individual outlets and 1 serves as a main power switch that controls all but the one marked "unswitched" on the back panel
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	1850 joules
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150V
UL1499 let through rating	330V - UL Verified
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes

Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (HWD/in)	11.5 x 11.2 x 1.5
Unit Dimensions (HWD/cm)	29.2 x 28.5 x 3.8
Shipping Dimensions (HWD/in)	13 x 11.5 x 1.75
Shipping Dimensions (HWD/cm)	33 x 29.2 x 4.4
Unit weight (lbs)	2.8
Unit weight (kg)	1.3
Material of construction	Plastic
Style	Under Monitor
Form factors supported	Supports under monitor placement as a power control center for an entire PC system with peripherals
SPECIAL FEATURES	
Right-Angle Plug	Yes
WARRANTY	
Standard warranty period	Lifetime
Connected equipment insurance (USA, Canada, Puerto Rico)	\$50,000

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2636.