



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TMC-6

**6-outlet, 6-ft cord, 1440 joules, Tel/Modem protection, Under-Monitor Protect It! Surge Suppressor**

### Highlights

- 6 outlets / 6-ft. cord
- 1440 joule rating
- Tel/modem surge protection
- Individual switches
- \$50,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)



### Description

Tripp Lite's TOUCHMASTER COMPACT surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TOUCHMASTER COMPACT offers 6 total outlets, 6 foot cord and LEDs to warn of power and wiring problems. Heavy grade AC suppression rated at 1440 joules shields equipment from surges and line noise. Attractive, slim design is perfect for use under desktop computer monitors or notebook computers. Individual switches offer power control over connected equipment. Lifetime warranty with \$50,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Slim, compact design perfect for use under desktop monitors and notebook computers

SUPPRESSION: AC: 150V RMS Clamping/1440 joules/400V UL1449 3rd Edition

#### Applications

- Ideal for PCs, notebook computers, peripherals and home electronics

#### Package Includes

- TOUCHMASTER COMPACT surge suppressor
- 6-ft. phone cord
- Instruction manual and warranty information

### Features

- 6 outlets
- 6-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment; 6-ft. telephone cord included
- Surge suppression rating: 1440 joules
- EMI/RFI noise filtering

- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green), "grounded" (red) status and "power on" (green)
- Always-on outlet provides power for equipment you always need on, even when the "master" switch is off
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Allows for the computer to be controlled by the "master" switch and other outlets to be controlled either the "master" switch or corresponding switch on the front panel
- \$50,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada Only) covers connected equipment
- Lifetime product warranty

## Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	6 NEMA 5-15R
INPUT	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P input plug
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	6
Input cord length (m)	1.8
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	84000
LEDS ALARMS & SWITCHES	
Switches	Includes 5 front panel AC power switches. 4 switches control individual outlets and 1 serves as a main power switch that controls all but the one marked "unswitched" on the back panel
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	1440
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150V
UL1499 let through rating	400V - UL Verified
DATALINE SURGE SUPPRESSION	

<b>Telephone/DSL Protection</b>	Yes
<b>Telephone/DSL Protection Details</b>	1 line
<b>Cable (Coax) Protection</b>	No
<b>Network (Ethernet) Protection</b>	No
<b>PHYSICAL</b>	
<b>Shipping weight (lbs)</b>	3.4
<b>Unit Dimensions (HWD/in)</b>	1.75 x 11.5 x 12
<b>Shipping Dimensions (HWD/in)</b>	2.25 x 12.5 x 14
<b>Unit weight (lbs)</b>	2.8
<b>Material of construction</b>	Plastic
<b>Style</b>	Under Monitor
<b>Form factors supported</b>	Supports under monitor placement as a power control center for an entire PC system with peripherals
<b>SPECIAL FEATURES</b>	
<b>Right-Angle Plug</b>	Yes
<b>WARRANTY</b>	
<b>Product Warranty Period (U.S., Canada &amp; Puerto Rico)</b>	Lifetime limited warranty
<b>Connected Equipment Insurance (U.S., Canada &amp; Puerto Rico)</b>	\$50,000 <a href="#">Ultimate Lifetime Insurance</a>

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2636](http://www.tripplite.com/en/products/model.cfm?txtModelID=2636).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.