



Protect It! 2-Outlet Portable Surge Protector, Direct Plug-In, 1050 Joules, Fax/Modem Protection

MODEL NUMBER: TRAVELER



Description

The portable TRAVELER surge suppressor offers complete AC and phone line surge suppression for laptops, electronic notepads, personal organizers and other portable electronic devices. Compact portable housing weighing less than four ounces neatly fits into laptop travel cases. Retractable plug prevents scratching of expensive portable electronics. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines. TRAVELER offers two total outlets in a space-saving direct plug-in format and diagnostic LEDs to warn of wiring problems and suppressor damage.

Features

- 1050 joules AC surge suppression shields equipment from the strongest surges and line noise
- 2 AC outlets with room for 2 transformer plugs without blocking outlets covers computer and one peripheral
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- Exceeds IEEE 587 category A & B surge suppression specifications
- Extra-small portable housing weighing less than 4 ounces neatly fits into laptop travel cases retractable input plug prevents scratching of laptops and other devices
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- UL1449 Rated (330V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332116185 |

Highlights

- 2 outlets/Direct plug-in
- 1050 joule rating
- Retractable plug
- Modem/fax surge protection

Package Includes

- TRAVELER Surge Suppressor
- 6-ft. telephone cord
- Instruction manual with warranty information





| INPUT | | |
|------------------------------------|--|--|
| Nominal Input Voltage(s) Supported | 120V AC | |
| Recommended Electrical Service | 120V (110-125V) | |
| Input Cord Length Details | Direct plug-in | |
| Voltage Compatibility (VAC) | 120 | |
| Maximum Surge Amps | 30000 | |
| Input Plug Type | NEMA 5-15P | |
| Input Cord Length (ft.) | 0 | |
| Right-Angle Plug | No | |
| Input Cord Length (m) | 0.00 | |
| Integrated Cord Clip | No | |
| OUTPUT | | |
| Frequency Compatibility | 50 / 60 Hz | |
| Output Receptacles | (2) 5-15R | |
| Circuit Breaker (amps) | 15 | |
| Transformer Accommodation | (2) Yes | |
| Right-Angle Outlets | No | |
| USER INTERFACE, ALERTS & CON | TROLS | |
| Diagnostic LED(s) | Yes | |
| Diagnostic LED Details | Two built-in LEDs confirm suppressor "protection present" (green) and outlet "grounded" (red) status | |
| SURGE / NOISE SUPPRESSION | | |
| AC Suppression Joule Rating | 1050 | |
| AC Suppression Response Time | < 1 ns | |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression | |
| UL1449 Let Through Rating | 400V - UL Verified | |
| Automatic Shut-Off | No | |
| | | |
| DATALINE SURGE SUPPRESSION | 1 line | |
| Telephone/DSL Protection Details | 1 line | |
| Cable (Coax) Protection | No | |
| Network (Ethernet) Protection | No | |
| Telephone/DSL Protection | Yes | |
| PHYSICAL | | |





| Material of Construction | Plastic |
|---|---|
| Form Factors Supported | Direct plug-in connection enables mounting to any AC wall receptacle |
| Housing Color | Black |
| Mounting Holes or Slots | No |
| Receptacle Color | Black |
| Shipping Dimensions (hwd / in.) | 4.00 x 4.00 x 2.00 |
| Shipping Dimensions (hwd / cm) | 10.16 x 10.16 x 5.08 |
| Shipping Weight (lbs.) | 0.42 |
| Shipping Weight (kg) | 0.19 |
| Unit Dimensions (hwd / in.) | 3.500 x 2.500 x 1.750 |
| Unit Dimensions (hwd / cm) | 8.9 x 6.4 x 4.4 |
| Unit Weight (Ibs.) | 0.3 |
| Unit Weight (kg) | 0.14 |
| FEATURES & SPECIFICATIONS | |
| Rotatable Outlets | No |
| Antimicrobial | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | cUL Listed; UL 1449; UL 497A; UL 1363; UL Listed |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$50,000 Ultimate Lifetime Insurance |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.