



Protect It! 2-Outlet Portable Surge Protector, Direct Plug-In, 1050 Joules, Ethernet Protection

MODEL NUMBER: TRAVELER100BT







Highlights

- 2 outlets/Direct plug-in
- 1050 joule rating
- Retractable plug
- Single line Ethernet or modem/fax surge protection

Package Includes

- TRAVELER100BT Surge Suppressor
- 6-ft. telephone cord
- Instruction manual with warranty information

Description

The portable TRAVELER100BT surge suppressor offers complete AC and Ethernet or phone line surge suppression for laptops, electronic notepads, personal organizers and other portable electronic devices. Compact portable housing weighing less than four ounces neatly fits into laptop travel cases. Retractable plug prevents scratching of expensive portable electronics. Set of RJ45 Ethernet or telephone line suppression jacks protect network lines or dialup and DSL modem lines. TRAVELER100BT offers two total outlets in a space-saving direct plug-in format and diagnostic LEDs to warn of wiring problems and suppressor damage.

Features

- 1050 joules AC surge suppression shields equipment from the strongest surges and line noise
- 2 AC outlets with room for 2 transformer plugs without blocking outlets covers computer and one peripheral
- Ethernet or phone line surge suppression protects network lines or dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ45 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- Exceeds IEEE 587 category A & B surge suppression specifications
- Extra-small portable housing weighing less than 4 ounces neatly fits into laptop travel cases retractable input plug prevents scratching of laptops and other devices
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- UL1449 Rated (330V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332123336





INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Length Details	Direct plug-in	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	30000	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	0	
Right-Angle Plug	No	
Input Cord Length (m)	0.00	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(2) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(2) Yes	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Diagnostic LED Details	Two built-in LEDs confirm suppressor "protection present" (green) and outlet "grounded" (red) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1050	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
UL1449 Let Through Rating	400V - UL Verified	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection Details	1 line	
Cable (Coax) Protection	No	
Network (Ethernet) Protection	Yes	
Telephone/DSL Protection	Yes	
PHYSICAL		





Material of Construction	Plastic	
Form Factors Supported	Direct plug-in connection enables mounting to any AC wall receptacle	
Housing Color	Black	
Mounting Holes or Slots	No	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	4.90 x 2.00 x 4.00	
Shipping Dimensions (hwd / cm)	12.45 x 5.08 x 10.16	
Shipping Weight (lbs.)	0.30	
Shipping Weight (kg)	0.14	
Unit Dimensions (hwd / in.)	3.500 x 2.500 x 1.750	
Unit Dimensions (hwd / cm)	8.9 x 6.4 x 4.4	
Unit Weight (lbs.)	0.3	
Unit Weight (kg)	0.14	
COMMUNICATIONS		
Network Compatibility	100 Mbps (Fast Ethernet)	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.