



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TRAVELER3USB

### Travel-Size Surge Suppressor with USB Charging Ports for Cell Phones, Music Players, and PDAs



#### Highlights

- 3 AC power outlets
- 540 joule rating
- Concealable 18 inch Power Cord
- 2-USB Charging Ports
- Includes Mini USB Cable
- \$25,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

#### Description

Tripp Lite's portable TRAVELER3USB surge suppressor offers complete surge suppression for laptops, electronic notepads, personal organizers and other portable electronic devices. Compact and portable, it neatly fits into laptop travel cases. Comes with an 18 inch concealable cord allowing for ease of storage without scratching expensive electronics. With the addition of 2 USB Charging Ports, the TRAVELER3USB allows Road Warriors the ability to charge cell phone, MP3 Players and other portable devices more easily. TRAVELER3USB offers 3 total outlets which can accommodate a transformer, 2 USB Charging Ports and a diagnostic LED to warn of wiring problems and suppressor damage. \$25,000 Ultimate Lifetime Insurance (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 3 NEMA5-15R  
ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)  
FORMAT: Corded mobile surge with 1 transformer access  
SUPPRESSION: AC: 540 joules

#### Applications

- Ideal for use with laptops, electronic notepads, personal organizers and other portable electronic devices.

#### Package Includes

- TRAVELER3USB Surge Suppressor
- Mini USB Cable

#### Features

- 540 joules AC surge suppression shields equipment from the strongest surges and line noise
- 3 AC outlets with room for 1 transformer plug without blocking outlets.
- 2 USB Charging Ports for Cell phones, MP3 Players and more
- Portable housing with 18 inch concealable cord allow for ease of mobility and travel in briefcases
- Diagnostic LED confirm outlet surge suppression status
- Lifetime warranty with \$25,000 Ultimate Lifetime Insurance (USA & Canada Only)

#### Specifications

OVERVIEW	
Amp Capacity	15
Intended Application	Home/Office, Travel
OUTPUT	

Output Watt Capacity (watts)	1800
Frequency compatibility	60 Hz
Outlet quantity / type	3 NEMA 5-15R AC Outlets
Transformer accommodation	Supports up to 1 large transformer plug accessory without covering remaining outlets
<b>INPUT</b>	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle plug
Input cord length (ft.)	1
Voltage compatibility (VAC)	120
Maximum Surge Amps	36000
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Built-in LED confirm suppressor "protection present" (green) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	540
Protection modes	Includes Line to Neutral (L-N), Neutral to Ground (N-G) and Line to Ground (L-G) line surge suppression
Clamping voltage (RMS)	150
UL1499 let through rating	330V - UL Verified
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping weight (lbs)	.66
Unit Dimensions (HWD/in)	4.75 x 3.5 x 1.5
Shipping Dimensions (HWD/in)	6.75 x 4.6 x 1.5
Unit weight (lbs)	.45
Material of construction	Plastic
<b>CONNECTIONS</b>	
Ports	2
<b>SPECIAL FEATURES</b>	
Appearance	Ultra-compact, portable suppressor with concealable power cord fits easily in carrying case for laptops and other portable electronics
Right-Angle Plug	Yes

**CERTIFICATIONS****UL1449 3rd Edition (AC  
Suppression)**

UL1449

**cUL / CSA (Canada)**

cUL

**WARRANTY****Product Warranty Period  
(U.S., Canada & Puerto  
Rico)**

Lifetime limited warranty

**Connected Equipment  
Insurance (U.S., Canada &  
Puerto Rico)**\$25,000 [Ultimate Lifetime Insurance](#)

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=4315](http://www.tripplite.com/en/products/model.cfm?txtModelID=4315).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.