



Powering Business Worldwide

# USB / FireWire® - USB 1.1 Gold Extension Cable - 6 ft. (1.83 m)

MODEL NUMBER: U004-006-R

## Description

Tripp Lite's 6-ft. USB (universal serial bus) A/A extension cable is used to extend an existing USB device cable. This handy USB cable features, molded strain relief, double shielding, 24k gold plated connectors and gold plated copper contacts for superior conductivity and error-free data transmission. It is constructed of the highest quality wire allowed by the USB specification and consists of 20 AWG power wires to maximize the full potential of USB. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Clamshell retail packaging.

## Features

- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/20 AWG data lines
- Gold plated connectors and gold plated copper contacts provide superior conductivity
- Molded connectors with built-in strain relief ensure that the cable lasts a long time
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

## Highlights

- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/20 AWG data lines
- Gold plated connectors provide superior conductivity for low and high speed devices (1.5 to 12 Mbps.)
- Retail packaging

## System Requirements

- USB port and device

## Package Includes

- 6-ft. USB AA gold extension cable USB-A M/F

## Specifications

OVERVIEW	
UPC Code	037332014689
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
PHYSICAL	
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	6.75 x 5.75 x 1.25
Shipping Dimensions (hwd / cm)	17.14 x 14.60 x 3.18
Shipping Weight (lbs.)	0.37
Shipping Weight (kg)	0.17
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.