

## USB 2.0 A to B Cable (M/M), 10 ft. (3.05 m)

MODEL NUMBER: U022-010-R



Make the connection between a USB device and your computer's USB port. This USB 2.0 A/B Gold Device Cable assures that you get maximum performance from USB 2.0 devices (e.g. printers, external hard drives). It supports fast data transfer rates of up to 480 Mbps, and is backward compatible with USB 1.1.

### Features

- Meets or exceeds USB 2.0 specifications
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Gold-plated connectors and gold-plated copper contacts for superior conductivity
- Molded connectors and integral strain relief for extra durability and long life

### Highlights

- Meets or exceeds USB 2.0 specifications
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices, including multimedia applications.
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28AWG data lines, and 24AWG power lines.
- Gold-plated connectors provide superior conductivity
- Comes in retail packaging

### System Requirements

- Any device requiring a USB cable (USB 2.0 performance only when used with USB 2.0 device and USB controller).

### Package Includes

- 10-ft. USB 2.0 Gold Cable USB-A to USB-B

## Specifications

OVERVIEW	
UPC Code	037332116529
Technology	USB 2.0 (High Speed)
Cable Type	Passive
INPUT	
Maximum Input Amps	2
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB B (MALE)
Connector Plating	Gold



Powering Business Worldwide

TRIPP LITE  
SERIES

Contact Plating	Gold
Connector Style	Straight
<b>CHARGING</b>	
Total Charging Watts	10
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.0mm
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	6.10 x 5.40 x 1.60
Shipping Dimensions (hwd / cm)	15.49 x 13.72 x 4.06
Shipping Weight (lbs.)	0.44
Shipping Weight (kg)	0.20
Unit Packaging Type	Clamshell
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 131°F (-10° to 55°C)
Relative Humidity	5% to 90% RH, Non-Condensing
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	10W (5V/2A)
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
Data Transfer Rate	480 Mbps
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.