



USB 2.0 A to B Cable with Ferrite Chokes (M/M), 6 ft. (1.83 m)

MODEL NUMBER: U023-006



Features

- USB 2.0 certified
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil, Ferrite chokes
- Gold plated connectors and gold plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

Highlights

- Meets or Exceeds USB 2.0 Specifications
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices, including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil and Ferrite chokes, feature twisted 28AWG data lines, and 24AWG power lines.
- Gold plated connectors provide superior conductivity

System Requirements

- Any USB device requiring a USB cable with extra shielding capabilities
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

 6 ft. USB 2.0 Gold Cable USB-A to USB-B with Ferrite Chokes

Specifications

OVERVIEW		
UPC Code	037332156624	
Technology	USB 2.0 (High Speed)	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	USB A (MALE)	
Side B - Connector 1	USB B (MALE)	
Connector Style	Straight	
PHYSICAL		
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	





Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.20	
Shipping Weight (kg)	0.09	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
ENVIRONMENTAL		
Operating Temperature Range	14° to 122°F (-10° to 50°C)	
Storage Temperature Range	5° to 140°F (-15° to 60°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 79% RH, Non-Condensing	
FEATURES & SPECIFICATIONS		
USB Specification	USB 2.0 (up to 480 Mbps)	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.