

## USB Micro-B to USB-C Cable - USB 2.0, (M/M), 6 ft. (1.83 m)

MODEL NUMBER: **U040-006-MICRO**



Connect a USB Micro-B device to the USB Type-C (USB-C) port on your tablet, laptop, ultrabook or computer

### Features

- 6-ft. USB 2.0 Micro-B to USB Type-C (USB-C) device cable
- Connect a USB Micro-B device to the USB Type-C port on your tablet, laptop, ultrabook or computer
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in.....it connects in either direction!
- Supports up to 1.5A for faster charging
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair / 20AWG Power Pair

## Specifications

OVERVIEW	
UPC Code	037332188595
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold

### Highlights

- 6-ft. USB 2.0 Micro-B to USB Type-C (USB-C) device cable
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in
- Supports up to 1.5A for faster charging

### System Requirements

- A device with a Micro-B connector
- A tablet, laptop, ultrabook or computer with an available Micro-B or USB Type-C (USB-C) port

### Package Includes

- USB 2.0 Micro-B Male to USB Type-C (USB-C) Male Cable - 6-ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

Connector Style	Straight
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5MM
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85%, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.