

## USB 2.0 Hi-Speed File Transfer Cable (USB-A M/M) 6-ft.

MODEL NUMBER: **U232-006**



### Description

Tripp Lite's U232-006, USB 2.0 hi-speed file transfer cable, provides a simple way to connect two computers via their USB ports, in order to quickly and easily exchange files. The cable provides true plug-n-play capability, while transferring files at much greater speeds than USB 1.1 file transfer products. The included PCLinq2 application program provides a drag-n-drop, user friendly interface to transfer files. You simply plug in the U232-006 cable and install the application software into your PC(s). Tripp Lite 1-Year Limited Warranty.

### Features

- USB 2.0 hi-speed compliant
- Single cable solution for files transfer
- Printer and storage sharing between two computers
- USB networking - Ethernet emulation
- Drag-n-drop user-friendly interface
- No external power needed
- Supports Windows 98/ME/2000/XP

## Specifications

OVERVIEW	
UPC Code	037332123251
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (MALE)
PHYSICAL	

### Highlights

- Ideal for transferring files between a notebook and desktop
- USB 2.0 hi-speed compliant
- Plug-n-play for easy installation and use

### System Requirements

- IBM PC Pentium 133 or higher compatible system
- Available USB 2.0 port (up to 480Mbps) or available USB 1.1 port (up to 12Mbps)
- CD-ROM Drive
- Windows 98/ME/2000/XP

### Package Includes

- 1 U232-006 USB 2.0 File Transfer Cable
- 1 Users Manual
- Driver Software on CD

Color	Silver
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	1.70 x 6.10 x 5.20
Shipping Dimensions (hwd / cm)	4.32 x 15.49 x 13.21
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.