



USB 3.0 SuperSpeed Extension Cable (A M/F), Blue, 10 ft. (3.05 m)

MODEL NUMBER: U324-010





Extends a USB 3.0 cable an additional 10ft.

Description

This SuperSpeed USB 3.0 extension cable brings significant performance enhancements to the ubiquitous USB standard, while remaining compatible with the billions of USB-enabled devices currently deployed in the market. SuperSpeed USB will deliver 10x the data transfer rate of Hi-Speed USB, up to 5 Gbps, as well as improved power efficiency. USB 3.0 utilizes a bi-directional data interface rather than USB 2.0's half-duplex arrangement, where data can only flow in one direction at a time, giving a ten-fold increase in theoretical bandwidth.

Features

- 10-ft. (3.05 m) USB 3.0 SuperSpeed Extension Cable
- SuperSpeed USB is 10 times faster than Hi-Speed USB, with transfer rates up to 5 Gbps.
- · SuperSpeed USB is a Sync-N-Go technology that minimizes user wait-time.
- SuperSpeed USB will provide Optimized Power Efficiency...No device polling and lower active and idle power requirements.
- SuperSpeed USB is backwards compatible with USB 2.0. Devices interoperate with USB 2.0 platforms. Hosts support USB 2.0 legacy devices.

Specifications

| OVERVIEW | | |
|----------------------|--------------------|--|
| UPC Code | 037332158093 | |
| Technology | USB 3.x | |
| Cable Type | Passive | |
| CONNECTIONS | | |
| Side A - Connector 1 | USB 3.0 A (MALE) | |
| Side B - Connector 1 | USB 3.0 A (FEMALE) | |

Highlights

- 10-ft. (3.05 m) SuperSpeed USB 3.0 Extension Cable, A-A
- 10 times faster than USB 2.0, with transfer rates up to 5 Gbps

System Requirements

• Computers and Peripherals with USB 3.0 capabilities

Package Includes

 10-ft. (3.05 m) USB 3.0 Super Speed A-A Extension cable





| Connector Plating | Nickel |
|--|-------------------------------------|
| Contact Plating | Gold |
| Connector Style | Straight |
| PHYSICAL | |
| Material of Construction | PVC |
| Cable Jacket Color | Blue |
| Cable Jacket Rating | VW-1 |
| Cable Outer Diameter (OD) | 5.5MM |
| Cable Length (ft.) | 10 |
| Cable Length (m) | 3.05 |
| Cable Length (in.) | 120 |
| Shipping Dimensions (hwd / in.) | 7.00 x 9.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 17.78 x 22.86 x 1.27 |
| Shipping Weight (lbs.) | 0.04 |
| Shipping Weight (kg) | 0.02 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 14° to 140°F (-10° to 60°C) |
| Storage Temperature Range | -4° to 185°F (-20° to 85°C) |
| Relative Humidity | 10% to 85%, Non-Condensing |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 3.0 (up to 5 Gbps) |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.