



# USB 3.0 SuperSpeed Device Cable (A to Micro-B M/M) Black, 1 ft. (0.31 m)

### MODEL NUMBER: U326-001-BK





#### **Highlights**

- 1-ft. SuperSpeed USB 3.0 A to Micro B Cable
- 10 times faster than USB 2.0, with transfer rates up to 5 Gbps

#### **System Requirements**

• Computers and Peripherals with USB 3.0 capabilities

#### Package Includes

 1-ft. SuperSpeed USB 3.0 A Male to Micro B Male Device Cable - Black

Connects a USB3.0 enabled computer to a USB3.0 peripheral with Micro B type connector

#### **Features**

- 1-ft. SuperSpeed USB 3.0 A Male to Micro B Male Black
- SuperSpeed USB is 10 times faster than Hi-Speed USB, with transfer rates up to 5 Gbps.
- Sync-N-Go technology minimizes user wait-time.
- Provides Optimized Power Efficiency...No device polling and lower active and idle power requirements.
- Backwards compatible with USB 2.0. Devices interoperate with USB 2.0 platforms. Hosts support USB 2.0 legacy devices.
- Aluminum Foil / Braid shielding for superior EMI / RFI protection

## **Specifications**

OVERVIEW	
UPC Code	037332186164
Technology	USB 3.x
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 MICRO-B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight





PHYSICAL		
Material of Construction	PVC	
Cable Jacket Color	Black	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	5.5MM	
Cable Length (ft.)	1	
Cable Length (m)	0.30	
Cable Length (in.)	12	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.13	
Shipping Weight (kg)	0.06	
ENVIRONMENTAL		
Operating Temperature Range	14° to 140°F (-10° to 60°C)	
Storage Temperature Range	-4° to 185°F (-20° to 85°C)	
Relative Humidity	10% to 85%, Non-Condensing	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.0 (up to 5 Gbps)	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.