

# Universal Reversible USB 2.0 Extension Cable (Up / Down Angle Reversible A to A M/F), 6-ft.

MODEL NUMBER: UR024-006-UDA



Up / Down Angle Reversible USB "A" connector plugs in any direction

## Description

This 6-ft USB extension cable features an Up / Down Angle Reversible A-Male connector, and is manufactured using USB 2.0 cable. Up / Down Angle Reversible connector allows the cable to be plugged in any direction. This cable is backwards compatible and can also be used with the older USB 1.1 cables. Made with superior foil shielding for reliable error-free data communications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) makes it perfect for multimedia applications.

## Features

- 6-ft., USB 2.0 Up / Down Angle Reversible A-Male to A-Female Extension Cable
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

## Specifications

OVERVIEW	
UPC Code	037332185358
Technology	USB 2.0 (High Speed)
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)

## Highlights

- Universal, Up / Down Reversible A-Male plugs in any direction
- Extend distances of USB 2.0 cables with this extension cable
- Supports faster data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices, especially multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/24 AWG data lines
- Gold plated contacts provide superior conductivity

## System Requirements

- Any USB device requiring a USB cable
- USB 2.0 performance only when used with USB 2.0 device and USB 2.0 controller

## Package Includes

- Up / Down Angle Reversible USB 2.0 A-Male to A-Female Extension Cable - 6-ft.



Powering Business Worldwide



Side B - Connector 1	USB A (FEMALE)
<b>PHYSICAL</b>	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.