



Universal Reversible USB 2.0 Cable (Reversible A to Up-angle 5Pin Mini B M/M), 6 ft. (1.83 m)

MODEL NUMBER: UR030-006-UPB



Universal / Reversible "A" connector allows plugging in any direction

Features

- Universal / Reversible "A" connector plugs in any direction
- Up-Angle Mini B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, Cell Phones, PDA's, etc with 5-Pin Mini-B USB connectors
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Nickel plated connectors and gold plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

Highlights

- Universal / Reversible A connector eliminates guesswork as to connector orientation
- Up-Angle Mini B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, PDA's, etc with Mini-B 5-Pin connectors

System Requirements

- Any USB device requiring a USB cable with Mini-B 5-Pin connector
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

 6-ft. USB2.0 Universal / Reversible A to Up-Angle Mini-B Device Cable (A Male to 5Pin Mini-B Male)

Specifications

OVERVIEW		
UPC Code	037332182258	
Technology	USB 2.0 (High Speed)	
CONNECTIONS		
Side A - Connector 1	REVERSIBLE USB A (MALE)	
Side B - Connector 1	USB MINI-B 5-PIN (MALE)	
PHYSICAL		
Color	Black	





Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	0.25 x 0.25 x 10.00	
Shipping Dimensions (hwd / cm)	0.64 x 0.64 x 25.40	
Shipping Weight (lbs.)	0.10	
Shipping Weight (kg)	0.05	
ENVIRONMENTAL		
Operating Temperature Range	14 to 122 F (-10 to 50 C)	
Storage Temperature Range	5 to 140 F (-15 to 60 C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.