

Universal Reversible USB 2.0 Cable, 28/24AWG (Reversible A to 5Pin Micro B M/M) - 10 Piece Bulk Pack, 1 ft. (0.31 m)

MODEL NUMBER: UR050-001-24-10



Universal / Reversible "A" connector allows plugging in any direction

Description

Tripp Lite's UR050-001-24-10 1-ft. (0.31 m) USB 2.0 A to Micro-B cable features a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. Micro-USB is the latest generation of USB connector, and is found on Cell Phones, PDA's, Digital Cameras, Tablets and more. Constructed of premium double-shielded cable with tinned copper braid and aluminum mylar foil featuring twisted 28AWG data lines and 24AWG power lines. 24AWG power lines allow for charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge. USB 2.0 rated cable handles 480Mbps data transfer rates. 10 Piece Bulk Pack.

Features

- USB Universal / Reversible A Male to Micro-B Male - 10 Piece Bulk Pack
- Constructed of 24AWG power lines for the charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge
- Premium double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines
- Supports USB 2.0 data transfer rates up to 480Mbps

Specifications

OVERVIEW	
UPC Code	037332186157
Technology	USB 2.0 (High Speed)
CONNECTIONS	

Highlights

- Universal / Reversible "A" Male to Micro-B Male - 10 Piece Bulk Pack
- Constructed of 24AWG power lines for the charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge
- Premium double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines
- Supports USB 2.0 data transfer rates up to 480Mbps

System Requirements

- Digital devices that use the USB Micro-B Female socket

Package Includes

- 1-ft. (0.31 m) USB 2.0 Universal / Reversible A to Micro-USB B Device Cable, 28/24AWG (A Male to Micro-B Male) - 10 Piece Bulk Pack



Powering Business Worldwide



Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
PHYSICAL	
Color	Black
Wire Gauge (AWG)	28/24
Cable Length (ft.)	1
Cable Length (m)	0.30
Shipping Dimensions (hwd / in.)	12.60 x 1.00 x 9.85
Shipping Dimensions (hwd / cm)	32.00 x 2.54 x 25.02
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.