



Important Note

This USB-A to USB Micro-B cable is designed for charging only. It will not transfer data. **Micro USB Cable for Charging (M/M) - Reversible**

Left/Right USB-A to Right-Angle USB Micro-B, Black, 3 ft. (0.91 m)

MODEL NUMBER: UR05C-003-RARB





Highlights

- Left/right and right-angle plugs ideal for connecting equipment in tight spaces, such as behind furniture or flush against walls
- Dedicated USB-A to USB Micro-B cable charges devices only and does not transfer data
- 20 AWG power lines allow rapid charging of compatible devices, including smartphones and tablets

System Requirements

 USB Micro-B devices, including smartphones and tablets

Package Includes

• USB-A to USB Micro-B Charge Cable (M/M), Black, 3 ft.

USB-A to USB Micro-B charge cable keeps your smartphone, tablet and other compatible device at capacity.

Description

This 3-ft. (0.91 m) USB 2.0 cable (M/M) with 20 AWG power lines is dedicated to charging compatible mobile devices, including smartphones and tablets. The reversible left/right USB-A connector and the right-angle USB Micro-B connector help you connect in areas where space is at a premium, such as behind furniture. The angled male plugs reduce stress and help the cable move freely without cracking or breaking loose from the connector. *Note: the UR05C-003-RARB is a charging cable only and is incapable of transferring data.*

Features

- Dedicated charging USB-A to USB Micro-B cable does not transfer data
- Made from 20 AWG power lines for rapid charging of compatible devices, including smartphones and tablets
- Left/right and right-angle male plugs excellent for connecting equipment in tight spaces, such as behind furniture

Specifications

OVERVIEW	
UPC Code	037332188076
Technology	USB 2.0 (High Speed)
Cable Type	Passive





CONNECTIONS		
Side A - Connector 1	REVERSIBLE USB A (MALE)	
Side B - Connector 1	MICRO-USB B (MALE)	
Connector Style	Angled	
PHYSICAL		
Cable Jacket Color	Black	
Cable Length (ft.)	3	
Cable Length (m)	0.91	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.06	
Shipping Weight (kg)	0.03	
ENVIRONMENTAL		
Operating Temperature Range	14° to 122°F (-10° to 50°C)	
Storage Temperature Range	5° to 140°F (-15° to 60°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.