

**Important Note**

This cable is designed for charging only, and will not work for transferring data.

**Dedicated Reversible USB Charging Cable  
(Reversible A to Right-Angle 5-Pin Micro B)  
Black, 3 ft. (0.91 m)**

MODEL NUMBER: UR05C-003-RB



Dedicated 20AWG Micro USB Charging cable ensures fastest charging of tablets, phones, and other mobile devices

**Description**

The UR05C-003-RB is a Micro-USB cable dedicated to charging mobile devices such as tablets and phones. Constructed of 20 AWG power lines, it ensures the fastest charging of your device. It also features a Reversible A Male connector, which takes the guesswork out of which way to position the A connector for plugging. Its Right-Angle Micro-B connector is ideal in situations where space is at a premium, and reduces stress and excessive bending on the cable.

**Features**

- Dedicated Charging cable; will not work for transferring data
- Reversible A Male to Right Angle Micro-B Male
- Constructed of 20AWG power lines for the fastest charging of Micro USB devices such as tablets and phones
- Right Angle Micro-B connector is ideal in situations where space is at a premium, and reduces stress and excessive bending on the cable

**Highlights**

- Dedicated Charging cable; will not work for transferring data
- Reversible A Male to Right Angle Micro-B Male
- Constructed of 20AWG power lines for the fastest charging of Micro USB devices such as tablets and phones
- Right Angle Micro-B connector is ideal in situations where space is at a premium, and reduces stress and excessive bending on the cable

**System Requirements**

- Micro USB mobile device such as a tablet or phone

**Package Includes**

- 3-ft. (0.91 m) Black Micro USB Dedicated Charging Cable, 20AWG (Reversible A Male to Right Angle Micro-B Male)

**Specifications**

OVERVIEW	
UPC Code	037332188069
Technology	USB 2.0 (High Speed)
Cable Type	Passive



Powering Business Worldwide



CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
Connector Style	Angled
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.