

This Micro USB cable is designed for charging only. It will not transfer data.

Micro USB Cable for Charging (M/M) - Reversible Up/Down USB-A to Right-Angle USB Micro-B, 20 AWG, Black, 3 ft. (0.91 m)

MODEL NUMBER: UR05C-003-UARB



Highlights

- Up/down and right-angle plugs ideal for connecting equipment in tight spaces, such as behind furniture or flush against walls
- Dedicated USB-A to USB Micro-B cable charges devices only and does not transfer data
- 20 AWG power lines allow rapid charging of compatible devices, including smartphones and tablets

System Requirements

- USB Micro-B devices, including smartphones and tablets

Package Includes

- Micro USB Cable (M/M), 20 AWG, Black, 3 ft.

20 AWG USB-A to USB Micro-B charge cable keeps your smartphone, tablet and other compatible device at capacity.

Features

- Dedicated charging USB-A to USB Micro-B cable does not transfer data
- Made from 20 AWG power lines for rapid charging of compatible devices, including smartphones and tablets
- Up/down and right-angle male plugs excellent for connecting equipment in tight spaces, such as behind furniture or flush against walls

Specifications

| OVERVIEW | |
|----------------------|-------------------------|
| UPC Code | 037332188083 |
| Technology | USB 2.0 (High Speed) |
| Cable Type | Passive |
| CONNECTIONS | |
| Side A - Connector 1 | REVERSIBLE USB A (MALE) |
| Side B - Connector 1 | MICRO-USB B (MALE) |
| PHYSICAL | |
| Cable Jacket Color | Black |



Powering Business Worldwide



| | |
|-------------------------------------|------------------------------|
| Cable Length (ft.) | 3 |
| Cable Length (m) | 0.91 |
| Shipping Dimensions (hwd / in.) | 7.00 x 9.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 17.78 x 22.86 x 1.27 |
| Shipping Weight (lbs.) | 0.06 |
| Shipping Weight (kg) | 0.03 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 14° to 122°F (-10° to 50°C) |
| Storage Temperature Range | 5° to 140°F (-15° to 60°C) |
| Operating Humidity Range | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range | 0% to 90% RH, Non-Condensing |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.