

SU20KX

Battery Pack		Battery Pack		<<<< Load in watts >>>>									
Part Number	Order Quantity	2000	4000	6000	8000	9000	10000	11000	12000	13000	14000	15000	16000
Included Batteries	0	67.6	30.9	18.8	13.0	11.4	10.0	8.9	8.0	7.2	6.6	6.0	5.5
Add QTY 2 RBC2030	0	156.7	74.2	46.1	32.5	28.5	25.3	22.7	20.5	18.7	17.1	15.7	14.5
BP480V26B	1	307.7	147.1	91.9	64.9	57.1	50.7	45.5	41.1	37.5	34.3	31.5	29.2
BP480V26B / Add QTY 2 RBC2030	1	375.3	177.9	110.7	78.0	68.5	60.8	54.4	49.2	44.7	40.9	37.6	34.7
BP480V40C	1	456.7	224.3	142.4	101.7	89.7	80.0	72.0	65.3	59.6	54.7	50.4	46.7
BP480V40C / Add QTY 2 RBC2030	1	524.3	255.2	161.3	114.7	101.1	90.1	80.9	73.3	66.8	61.3	56.4	52.2
BP480V55	1	617.0	309.5	199.0	143.4	126.9	113.5	102.4	93.1	85.1	78.3	72.3	67.1
BP480V78	1	861.1	441.6	288.2	209.7	186.3	167.2	151.3	137.9	126.4	116.5	107.9	100.4
BP480V103	1	1122.7	585.5	386.3	283.5	252.7	227.4	206.3	188.4	173.1	159.9	148.3	138.2
BP480V140	1	1501.3	797.3	532.1	394.0	352.3	318.0	289.3	264.9	244.0	225.9	210.0	196.0
BP480V78	2	1661.8	888.1	595.1	441.9	395.6	357.4	325.5	298.3	275.0	254.8	237.1	221.4
BP480V103	2	2151.0	1168.6	790.8	591.6	531.1	481.1	439.1	403.4	372.7	345.9	322.5	301.7
BP480V140	2	2841.9	1573.7	1076.4	811.6	730.7	663.7	607.3	559.2	517.7	481.6	449.8	421.7
BP480V103	3	3102.3	1729.2	1186.9	897.1	808.4	734.9	673.0	620.1	574.5	534.7	499.8	468.8
BP480V140	3	4049.6	2307.6	1601.7	1219.9	1102.4	1004.7	922.2	851.6	790.6	737.3	690.3	648.7
BP480V140	4	5142.4	3000.8	2106.9	1616.7	1464.8	1338.2	1230.9	1139.0	1059.3	989.6	928.1	873.5

SU40K SU40KX

Battery Pack		Battery Pack		<<<< Load in watts >>>>									
Part Number	Order Quantity	4000	8000	12000	16000	18000	20000	22000	24000	26000	28000	30000	32000
Included Batteries	0	71.5	31.5	18.9	13.0	11.4	10.1	9.0	8.0	7.3	6.6	6.0	5.5
BP480V26B	1	183.7	81.8	49.5	34.3	30.0	26.6	23.8	21.4	19.4	17.7	16.2	14.9
BP480V40C	1	258.5	117.5	71.9	50.2	44.1	39.2	35.1	31.7	28.9	26.4	24.3	22.4
BP480V55	1	341.0	158.1	97.7	68.6	60.5	53.8	48.4	43.8	39.9	36.6	33.7	31.2
BP480V78	1	469.3	222.7	139.5	98.8	87.3	78.0	70.2	63.7	58.2	53.5	49.3	45.7
BP480V103	1	609.1	294.6	186.7	133.3	118.1	105.7	95.4	86.8	79.4	73.0	67.5	62.7
BP480V140	1	814.9	402.4	258.3	186.2	165.5	148.5	134.4	122.5	112.3	103.5	95.9	89.2
BP480V78	2	903.2	449.2	289.7	209.5	186.4	167.5	151.7	138.4	127.0	117.1	108.6	101.0
BP480V103	2	1176.1	595.3	388.3	283.2	252.7	227.7	206.8	189.1	173.9	160.7	149.2	139.1
BP480V140	2	1570.7	810.2	534.8	393.5	352.4	318.5	290.0	265.8	245.0	227.0	211.2	197.2
BP480V103	3	1722.2	893.8	592.1	436.9	391.6	354.3	322.9	296.2	273.2	253.3	235.8	220.4
BP480V140	3	2286.2	1209.5	810.2	602.9	542.1	491.7	449.3	413.2	382.0	354.9	331.1	310.0
BP480V140	4	2963.2	1597.8	1081.4	810.7	730.9	664.6	608.7	561.0	519.8	483.8	452.2	424.1

SU60K SU60KX

Battery Pack		Battery Pack		<<<< Load in watts >>>>									
Part Number	Order Quantity	6000	12000	18000	24000	27000	30000	33000	36000	39000	42000	45000	48000
BP480V26B	1	78.7	34.5	20.7	14.2	12.2	10.6	9.3	8.2	7.4	6.6	6.0	5.5
BP480V40C	1	132.7	59.5	36.2	25.2	21.7	18.9	16.7	14.9	13.4	12.1	11.0	10.1
BP480V55	1	193.2	88.3	54.2	38.0	32.8	28.7	25.4	22.7	20.5	18.6	17.0	15.6
BP480V78	1	288.0	134.8	83.8	59.1	51.1	44.8	39.8	35.7	32.2	29.3	26.8	24.7
BP480V103	1	392.4	187.0	117.5	83.4	72.4	63.6	56.6	50.8	46.0	41.9	38.4	35.4
BP480V140	1	547.1	266.0	169.2	121.2	105.4	93.0	82.9	74.5	67.6	61.7	56.7	52.3
BP480V78	2	613.8	300.6	192.0	137.9	120.1	106.0	94.6	85.2	77.3	70.6	64.9	59.9
BP480V103	2	821.1	409.0	264.2	191.3	167.2	148.0	132.3	119.4	108.6	99.4	91.4	84.5
BP480V140	2	1123.1	569.7	372.3	272.0	238.5	211.8	190.0	171.9	156.7	143.7	132.5	122.7
BP480V103	3	1239.7	632.4	414.8	303.9	266.8	237.2	213.0	192.9	175.9	161.4	149.0	138.1
BP480V140	3	1677.3	870.9	577.6	426.7	376.0	335.3	302.0	274.2	250.7	230.6	213.2	198.1
BP480V140	4	2208.9	1166.7	781.5	581.6	514.1	459.8	415.2	377.9	346.4	319.3	295.8	275.3

SU80K SU80KX		Battery Pack	Battery Pack	<<<< Load in watts >>>>											
Part Number		Order	Quantity	8000	16000	24000	32000	36000	40000	44000	48000	52000	56000	60000	64000
	BP480V26B	1		55.6	23.9	14.1	9.6	8.2	7.1	6.2	5.4	4.8	4.3	3.9	3.5
	BP480V40C	1		94.8	41.6	25.0	17.3	14.8	12.9	11.3	10.1	9.0	8.1	7.4	6.7
	BP480V55	1		139.2	62.1	37.7	26.2	22.5	19.7	17.4	15.5	13.9	12.6	11.5	10.6
	BP480V78	1		209.6	95.6	58.7	41.1	35.5	31.0	27.5	24.6	22.2	20.1	18.4	16.9
	BP480V103	1		287.8	133.7	82.9	58.4	50.5	44.3	39.3	35.2	31.8	29.0	26.5	24.4
	BP480V140	1		404.7	191.9	120.4	85.4	74.1	65.2	58.0	52.0	47.1	42.9	39.4	36.3
	BP480V78	2		455.4	217.5	137.0	97.5	84.7	74.5	66.4	59.6	54.0	49.2	45.2	41.7
	BP480V103	2		613.4	298.4	190.1	136.3	118.7	104.8	93.5	84.2	76.4	69.8	64.1	59.2
	BP480V140	2		845.4	419.1	270.3	195.6	171.0	151.4	135.4	122.2	111.1	101.7	93.6	86.6
	BP480V103	3		935.4	466.5	302.0	219.2	191.8	170.0	152.2	137.5	125.1	114.6	105.5	97.7
	BP480V140	3		1275.2	647.5	424.1	310.5	272.7	242.5	217.8	197.2	179.9	165.1	152.4	141.3
	BP480V140	4		1692.0	873.7	578.2	426.7	376.0	335.3	302.0	274.2	250.7	230.6	213.2	198.1

SU20K3/3		Battery Pack	Battery Pack	<<<< Load in watts >>>>											
Part Number		Order	Quantity	2000	4000	6000	8000	9000	10000	11000	12000	13000	14000	15000	16000
	Included Batteries	0		76.2	34.8	21.2	13.0	12.0	11.0	9.7	8.6	7.7	6.9	6.2	5.0
	BP240V99	1		631.8	309.7	196.8	137.1	120.9	107.5	95.7	77.3	69.8	63.5	58.1	52.7
	BP240V120	1		720.0	356.6	228.1	160.3	141.2	125.6	111.9	92.1	83.2	75.8	69.4	63.2
	BP240V1207C	1		720.0	356.6	228.1	160.3	141.2	125.6	111.9	92.1	83.2	75.8	69.4	63.2
	BP240V150	1		936.2	473.2	306.6	218.7	192.8	171.7	153.5	129.8	117.6	107.3	98.5	90.2
	BP240V1507C	1		936.2	473.2	306.6	218.7	192.8	171.7	153.5	129.8	117.6	107.3	98.5	90.2
	BP240V99	2		1144.1	586.9	384.0	276.7	244.2	217.7	195.1	167.8	152.3	139.2	128.0	117.6
	BP240V120	2		1315.2	681.4	448.7	325.5	287.6	256.7	230.4	200.0	181.8	166.4	153.1	140.9
	BP240V1207C	2		1315.2	681.4	448.7	325.5	287.6	256.7	230.4	200.0	181.8	166.4	153.1	140.9
	BP240V150	2		1728.3	912.9	608.4	446.7	395.5	353.8	318.6	280.7	255.9	234.8	216.6	200.1
	BP240V1507C	2		1728.3	912.9	608.4	446.7	395.5	353.8	318.6	280.7	255.9	234.8	216.6	200.1
	BP240V150	3		2476.0	1341.7	907.8	675.9	600.3	538.8	487.2	435.4	398.3	366.6	339.2	314.7
	BP240V1507C	3		2476.0	1341.7	907.8	675.9	600.3	538.8	487.2	435.4	398.3	366.6	339.2	314.7
	BP240V150	4		3181.3	1757.7	1201.9	902.8	803.8	723.2	655.6	590.4	541.4	499.4	463.0	430.5
	BP240V1507C	4		3181.3	1757.7	1201.9	902.8	803.8	723.2	655.6	590.4	541.4	499.4	463.0	430.5

SU30K3/3		Battery Pack	Battery Pack	<<<< Load in watts >>>>											
Part Number		Order	Quantity	2000	4000	6000	8000	10000	12000	14000	16000	18000	20000	22000	24000
	Included Batteries	0		124.8	58.1	35.9	25.2	19.0	13.0	12.2	10.1	8.6	7.4	6.4	5.0
	BP240V99	1		729.1	356.4	226.2	161.5	123.4	81.7	68.7	57.8	49.6	43.2	38.1	38.3
	BP240V120	1		817.3	403.4	257.5	184.6	141.6	96.5	81.0	68.3	58.7	51.2	45.2	44.7
	BP240V1207C	1		817.3	403.4	257.5	184.6	141.6	96.5	81.0	68.3	58.7	51.2	45.2	44.7
	BP240V150	1		1033.5	520.0	336.0	243.1	187.6	134.2	112.6	95.3	82.2	71.9	63.6	61.2
	BP240V1507C	1		1033.5	520.0	336.0	243.1	187.6	134.2	112.6	95.3	82.2	71.9	63.6	61.2
	BP240V99	2		1241.4	633.7	413.3	301.1	233.7	172.2	144.5	122.7	106.0	93.0	82.5	78.3
	BP240V120	2		1412.4	728.2	478.1	349.9	272.6	204.4	171.6	146.0	126.5	111.1	98.7	92.9
	BP240V1207C	2		1412.4	728.2	478.1	349.9	272.6	204.4	171.6	146.0	126.5	111.1	98.7	92.9
	BP240V150	2		1825.6	959.6	637.7	471.1	369.7	285.1	240.0	205.2	178.4	157.2	140.2	130.4
	BP240V1507C	2		1825.6	959.6	637.7	471.1	369.7	285.1	240.0	205.2	178.4	157.2	140.2	130.4
	BP240V150	3		2573.2	1388.5	937.2	700.3	554.8	439.8	371.9	319.8	279.5	247.5	221.6	204.4
	BP240V1507C	3		2573.2	1388.5	937.2	700.3	554.8	439.8	371.9	319.8	279.5	247.5	221.6	204.4
	BP240V150	4		3278.5	1804.5	1231.3	927.2	739.1	594.8	504.6	435.6	382.2	339.6	304.8	280.4
	BP240V1507C	4		3278.5	1804.5	1231.3	927.2	739.1	594.8	504.6	435.6	382.2	339.6	304.8	280.4