



OMNIVSINT1500XL Estimated Runtime

Load in Watts

UPS	Battery Pack	20W	40W	60W	80W	100W	200W	300W	400W	500W	600W	700W	800W	900W	940W
OMNIVSINT1500XL	Internal Batteries	323	188	129	96	76	34	21	14	11	8.1	6.4	5.2	4.3	4.0
OMNIVSINT1500XL	1 BP24V15RT2U	803	487	343	262	209	99	61	43	33	25	20	17	14	14
OMNIVSINT1500XL	1 BP24V28-2U	1,347	835	597	461	373	182	114	82	62	49				
OMNIVSINT1500XL	1 BP24V70-3U	2,857	1,833	1,341	1,053	863	441	287	209	162	129				
OMNIVSINT1500XL	2 BP24V70-3U	6,134	4,163	3,143	2,520	2,099	1,129	758	567	447	362				
OMNIVSINT1500XL	3 BP24V70-3U	8,185	5,745	4,418	3,585	3,012	1,660	1,130	853	678	552				
OMNIVSINT1500XL	4 BP24V70-3U	9,867	7,121	5,564	4,561	3,861	2,171	1,492	1,134	906	741				
OMNIVSINT1500XL	5 BP24V70-3U	11,272	8,329	6,598	5,459	4,652	2,661	1,844	1,409	1,131	929				
OMNIVSINT1500XL	6 BP24V70-3U	12,463	9,398	7,537	6,287	5,391	3,133	2,187	1,679	1,353	1,114				
OMNIVSINT1500XL	7 BP24V70-3U	13,486	10,350	8,393	7,054	6,082	3,586	2,521	1,943	1,571	1,297				
OMNIVSINT1500XL	8 BP24V70-3U	14,373	11,205	9,176	7,767	6,730	4,023	2,846	2,203	1,785	1,477				
OMNIVSINT1500XL	9 BP24V70-3U	15,151	11,975	9,896	8,429	7,339	4,443	3,163	2,456	1,996	1,655				
OMNIVSINT1500XL	10 BP24V70-3U	15,837	12,674	10,560	9,048	7,912	4,849	3,471	2,705	2,203	1,831				

All runtime values are in minutes.