

## 10-Device Desktop USB Charging Station for Tablets, iPads and E-Readers

MODEL NUMBER: CSD1006USB



Locking enclosure provides USB charging, secure storage and cord management for up to 10 tablets, iPads and e-readers. Recommended for education, office, commercial, retail, industrial and healthcare environments.

### Description

The CSD1006USB 10-Device Desktop USB Charging Station provides USB charging, secure storage and cord management for up to 10 tablets, iPads and e-readers up to 10.5 inches. It's recommended for schools, offices, warehouses, retail outlets, worksites, healthcare facilities and anywhere else multiple mobile devices are used.

Devices fit into slots 1.25 inches wide and plug into the 10 USB ports as needed for proficient charging. The CSD1006USB delivers up to 5V 2.4A per port, which is plenty of power for charging battery-intensive devices. To protect your devices, the CSD1006USB prevents them from drawing more power than it is capable of supporting and stops charging a device when the device's battery is at 100%.

The CSD1006USB locks with the included keys to help prevent theft, damage or tampering. A cable with combination lock is also included to secure the charging station to a desk, table, cart or other flat surface. The 6-ft. (1.83 m) AC input cord with NEMA 5-15P plug helps you place the charging station in a convenient location. Storage shelf dividers are easily removed to accommodate thicker devices. Cabling is secured beneath the shelf tray to alleviate clutter.

*iPad is a registered trademark of Apple.*

### Features

#### Convenient USB Charging

- 10 USB ports for charging tablets, iPads and e-readers up to 10.5 in.
- Devices fit into slots 1.25 in. wide
- Device USB charge cables plug into USB ports
- 6-ft. (1.83 m) AC input cord with right-angle NEMA 5-15P plug reaches convenient outlets
- Recommended wherever multiple mobile devices are used—schools, offices, warehouses, etc.

#### Comprehensive Protection

- Delivers up to 5V 2.4A per port via BC 1.2 rapid charging
- Protects against overheating, over-current and overcharging

#### Complete Security

- Locks with included keys to help prevent device theft, damage or tampering

### Highlights

- 1.25 in. wide slots hold USB devices up to 10.5 in.
- 6-ft. (1.83 m) AC input cord with right-angle NEMA 5-15P plug
- Delivers up to 5V 2.4A per port via BC 1.2 rapid charging
- Locking lid helps prevent device theft, damage or tampering
- Separate cable with combination lock for added security

### Package Includes

- CSD1006USB 10-Device Desktop USB Charging Station
- External power supply w/NEMA 5-15P plug (Input: 100–240V, 50/60 Hz; Output: 12V, 8A)
- Enclosure unit with locking lid
- USB charger enclosure mount
- Combination cable lock
- (2) Keys
- Owner's manual

- Included combination cable lock secures the unit to a desk or cart

**Clutter-Reducing Organization**

- USB ports and cables store out of sight
- Storage shelf dividers can be removed to accommodate thicker devices

## Specifications

OVERVIEW	
UPC Code	037332200082
Product Type	Multi-Device Charger
Charging Form Factor	Desktop Cabinet
Charger Functions	Charge; Secure
Device Compatibility	Laptop; Tablet
Device Slots	10
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 2A; Output: 12V, 8A, 6 ft.
CHARGING	
Number of Charging Ports	10
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	BC 1.2
Charging Ports / Amps	(10) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
PHYSICAL	
Color	Black; Gray
Material of Construction	Plastic



Powering Business Worldwide



Charging Station Form Factor	Desktop Cabinet
Shipping Dimensions (hwd / in.)	16.40 x 10.90 x 17.40
Shipping Dimensions (hwd / cm)	41.66 x 27.69 x 44.20
Shipping Weight (lbs.)	13.87
Shipping Weight (kg)	6.29
Unit Dimensions (hwd / in.)	8.940 x 16.540 x 13.540
Unit Dimensions (hwd / cm)	42.01 x 34.39 x 22.71
Number of Shelves	1
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	41° to 95°F (5° to 35°C)
Storage Temperature Range	-4° to 122°F (-20° to 50°C)
Relative Humidity	20% to 80%
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	No
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	Yes
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key; Combination Cable Lock
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	EN 55022; EN 55024
Product Compliance	RoHS; CE (Europe); REACH; FCC Part 15 Class B (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	No



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.