

Toolless Shielded Cat6a Keystone Jack, PoE/PoE+ Compliant, Shuttered - Silver, TAA

MODEL NUMBER: N238-001-SH-TFA



Highlights

- Easy to terminate—no punchdown tool required
- Protective shielded housing reduces EMI/RFI interference
- Features a shutter / dust cap that protects from dust and contaminants when not in use
- Keystone design for use with wallplates, patch panels and surface mount boxes
- Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion
- Meets all EIA/TIA Cat6a requirements

Package Includes

- N238-001-SH-TFA Toolless Shielded Cat6a Keystone Jack, PoE+ Compliant, Silver

Terminate your shielded Cat6a wall jack without using a punchdown tool. Ideal for wallplates, patch panels and surface-mount boxes.

Description

Strengthen your high-speed network with the N238-001-SH-TFA Toolless Shielded Cat6a Keystone Jack. Terminate your Cat6a wall jack without using a punchdown tool. Just lace the conductors into the stuffer cap, press the 110 connector, and lock the jack into place. Use in wallplates, patch panels and surface-mount boxes. Power over Ethernet Plus (PoE+) compliant. RJ45 port is compatible with all shielded Cat6a cables, and toolless punchdown connection is compatible with 22-24 AWG solid wire cabling. The N238-001-SH-TFA's protective housing is fully shielded to reduce EMI/RFI interference that can damage or degrade data.

Features

Strengthens Your High-Speed Network Ideal for wallplates, patch panels and surface-mount boxes Lets you terminate your Cat6a wall jack without using a punchdown tool Toolless punchdown connection compatible with 22-24AWG Solid Wire cabling RJ45 port compatible with all Shielded Cat6a cables Power over Ethernet Plus (PoE+) compliant, specially designed to prevent spark-gap erosion

Superior Construction for Superior Performance Fully shielded housing cuts down on EMI/RFI interference that can damage or degrade data Features a shutter / dust cap that protects from dust and contaminants when not in use UL-listed Meets all EIA/TIA Cat6a requirements

TAA-Compliant Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchasing

Specifications

OVERVIEW	
UPC Code	037332189967
Product Type	RJ45 Keystone Jack
Technology	Cat6a
CONNECTIONS	



Powering Business Worldwide



Number of Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	110 IDC
PoE Type	Type 4 High-Power (100W, IEEE 802.3bt)
PHYSICAL	
Color	Silver
Connector Color	Silver; White
Shipping Dimensions (hwd / in.)	5.00 x 4.00 x 0.50
Shipping Dimensions (hwd / cm)	12.70 x 10.16 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
Unit Dimensions (hwd / in.)	5.000 x 4.000 x 0.500
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.