

# Mini DisplayPort to DVI Dual-Link Active Adapter Video Converter (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P137-06N-DVI-DL



Converts any Mini DisplayPort video signal for display on a DVI-D single-link or dual-link monitor, projector or television.

## Features

### Send High-Definition Mini DisplayPort Video Signals to a DVI Display

- Connects Mini DisplayPort computer to DVI-D dual-link monitor, projector or TV
- Active adapter for use with any Mini Displayport (or Thunderbolt 1 & 2) port
- Ideal for displaying video on large monitor or digital sign
- Female DVI dual-link and male Mini DisplayPort connectors

### Vibrant, Superior Video Quality

- Supports DVI dual-link video resolutions up to 2560 x 1600
- Supports DVI single-link video resolutions up to 1920 x 1080 (1080p)
- Supports 24-bit Deep Color (8 bits per channel)
- Converts Multi-Mode (DP++) and Single-Mode DisplayPort output
- Works with graphics cards that don't output DP++ signals, such as AMD Eyefinity

### Superior Materials for Superior Performance

- Gold-plated connectors and contacts for excellent conductivity
- Integral strain relief for long life
- Plug-and-play—no software, drivers or power supply necessary
- Fits easily into briefcase, backpack or laptop bag

## Specifications

OVERVIEW	
UPC Code	037332199263

## Highlights

- Active converter works with all Mini DisplayPort signals
- Compatible with Thunderbolt 1 and 2 ports on Mac computers
- Supports DVI dual-link video resolutions up to 2560 x 1600
- Supports DVI single-link video resolutions up to 1920 x 1080
- Converts Multi-Mode (DP++) and Single-Mode DisplayPort output
- Plug and play—no software, drivers or power supply needed

## System Requirements

- Computer with Mini DisplayPort and USB port
- Display with DVI output
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P137-06N-DVI-V2

## Package Includes

- P137-06N-DVI-DL Mini DisplayPort to DVI Dual-Link Active Converter (M/F), 6 in.



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Type	Video Adapter
Technology	DVI; DisplayPort
<b>CONNECTIONS</b>	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side A - Connector 2	USB A (MALE)
Side B - Connector 1	DVI-D DUAL LINK (FEMALE)
<b>PHYSICAL</b>	
Color	Silver
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	1.20 x 3.50 x 6.10
Shipping Dimensions (hwd / cm)	3.05 x 8.89 x 15.49
Shipping Weight (lbs.)	0.31
Shipping Weight (kg)	0.14
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.