




# 24-Outlet Vertical Power Strip, 120V, 20A, 5-20P, 15 ft. (4.57 m) Cord, 72 in.

MODEL NUMBER: PS7224-20





## **Highlights**

- 24 outlets
- Convenient and safe covered, on/off switch
- 20-amp circuit breaker
- 15-ft. (4.57 m) cord
- 72" length

#### **Package Includes**

- PS7224-20
- Mounting hardware
- Instruction manual

### **Description**

The PS7224-20 power strip offers 20A 120V multi-outlet AC power distribution in a convenient 72-inch mountable housing. Offers horizontal or vertical power distribution in rack-mount, raceway and workbench applications. Includes 24 output receptacles with 2.8-inch center-to-center spacing, 15-foot (4.6-meter) AC line cord and lighted power switch with locking transparent cover to prevent accidental shutoff. Sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

#### **Features**

- Sturdy all-metal 72 inch corded strip format with 2.795 inch center-to-center outlet spacing
- Included mounting hardware supports vertical or horizontal mounting in rack enclosures, raceways and more
- Includes 22 NEMA 5-15R and 2 NEMA 5-20R output receptacles
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- · Lighted power switch with locking transparent cover prevents accidental shutoff
- 20 amp electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

# **Specifications**

OVERVIEW		
UPC Code	037332011527	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	20A 120V	
Input Cord Gauge Type	12 gauge; SJT	





Voltage Compatibility (VAC)	120		
Input Plug Type	NEMA 5-20P		
Input Cord Length (ft.)	15		
Right-Angle Plug	No		
Input Cord Length (m)	4.57		
Integrated Cord Clip	No		
OUTPUT			
Frequency Compatibility	50 / 60 Hz		
Output Receptacles	(2) 5-15/20R; (22) 5-15R		
Circuit Breaker (amps)	20		
Transformer Accommodation	(12) Yes		
Right-Angle Outlets	No		
Outlet Spacing	2.795 in.		
USER INTERFACE, ALERTS & CONTROLS			
Switches	Lighted 2 position switch controls power to all outlets		
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off		
PHYSICAL	PHYSICAL		
Color	Silver		
Material of Construction	Aluminum		
Power Cord Color	Black		
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications		
Housing Color	Silver		
Included Mounting Accessories	Includes mounting clips		
Mounting Holes or Slots	No		
Outlets Measurement (Center to Center)	2.83 in.		
Receptacle Color	Black		
Shipping Dimensions (hwd / in.)	2.40 x 4.02 x 75.79		
Shipping Dimensions (hwd / cm)	6.10 x 10.21 x 192.51		
Shipping Weight (lbs.)	7.41		
Shipping Weight (kg)	3.36		
Unit Dimensions (hwd / in.)	1.750 x 72.000 x 1.250		
Unit Dimensions (hwd / cm)	183 x 3.8 x 3.8		
Unit Weight (lbs.)	6.5		
Unit Weight (kg)	2.95		





Outlet Spacing	2.795 in.	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
Built-In Circuit Breaker	Yes	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.