



SmartRack 12U Standard-Depth 4-Post Open Frame Rack

MODEL NUMBER: SR12UBEXPNDKD







Floor-standing open-frame 4-post rack stores and organizes 12U of 19-inch rack equipment in small offices, retail locations and other secure IT areas with limited floor space where you need easy access to equipment.

Description

The SmartRack 12U Standard-Depth 4-Post Open Frame Rack provides an economical rack-mount solution for small offices, retail locations and other secure IT locations with limited floor space where you need equipment to be organized and easy to access. It's ideal for mounting network switches, routers, patch panels, audio/video components and other EIA-standard 19-inch rack equipment up to 36 inches deep.

Constructed from heavy-duty steel with a durable black powder-coated finish, the SR12UBEXPNDKD has a maximum load capacity of 1000 lbs (453.6 kgs). Stashed away under a counter, on a workbench or in a corner, this rack saves precious space and allows you fast, easy access at your immediate workspace for organizing, installing and servicing equipment and cabling. The open design allows unobstructed airflow to help keep components cool and performing at their peak.

The self-squaring SR12UBEXPNDKD assembles using the included hardware. Built-in casters allow you to roll the rack into place. The vertical mounting rails have square, numbered holes and optional cable management hooks for securing equipment to the steel frame. Only user-supplied standard hand tools are required for setup. Toolless button holes accept 0U vertical installation of PDUs and cable managers.

Features

Saves Valuable Workspace

- Perfect for installing network switches, routers, patch panels and audio/video components in secure IT
 areas with limited floor space
- Houses EIA-standard 19 in. rack equipment up to 36 in. deep
- Maximum load capacity of 1000 lbs (453.6 kgs)

Convenient Open-Frame Design

- Allows fast, easy access for organizing, installing and servicing equipment and cabling
- · Rests under a counter, on a workbench or in a corner at your immediate workspace
- Unobstructed airflow keeps components cool and performing at their peak

Easy Assembly and Installation

Heavy-duty steel construction with durable black powder-coated finish

Highlights

- Maximum load capacity of 1000 lbs (453.6 kgs)
- Secures 12U of 19 in. rack equipment up to 36 in. deep
- Heavy-duty steel construction designed to last
- Assembles using included hardware
- Accommodates toolless button mounting for PDUs

Package Includes

Assembly Hardware

- (4) Vertical mounting rails
- (4) Side brackets
- (2) Base brackets with built-in casters
- (2) Top brackets
- (2) Adjustable side support/mounting rails
- (12) M6 x 12 mm screws
- (16) M8 screws

Equipment Mounting Hardware

- (20) M6 cage nuts
- (20) PVC cup washers
- (20) M6 screws
- (10) Cable management hooks
- (10) Hook mounting screws
- Owner's Manual





- Assembles with included hardware and user-supplied hand tools
- Vertical mounting rails with square, numbered holes and optional cable management hooks
- Built-in casters for rolling the rack into position
- Toolless button holes accept 0U vertical installation of PDUs and cable managers

Specifications

OVERVIEW	
UPC Code	037332188472
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	12U
Rack Depth	Standard
Maximum Device Depth (cm)	91.44
Maximum Device Depth (in.)	36
Maximum Device Depth (mm)	914
Minimum Device Depth (cm)	60.96
Minimum Device Depth (in.)	24
Minimum Device Depth (mm)	610
Shipping Dimensions (hwd / in.)	3.89 x 8.41 x 42.86
Shipping Dimensions (hwd / cm)	9.88 x 21.36 x 108.86
Shipping Weight (lbs.)	32.00
Shipping Weight (kg)	14.51
Unit Dimensions (hwd / in.)	25.600 x 20.370 x 35.940
Unit Dimensions (hwd / cm)	65.02 x 51.74 x 91.29
Unit Weight (lbs.)	45
Unit Weight (kg)	20.41
Weight Capacity - Stationary (kg)	454
Weight Capacity - Stationary (lbs.)	1000
Number of Vertical Mounting Rails	4
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No





STANDARDS & COMPLIANCE		
Product Compliance	RoHS; EIA/ECA-310-E; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	5-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.