

## Protect It! 3-Outlet Surge Protector with Desk Clamp, 10 ft. Cord, 510 Joules, 2 USB Charging Ports, Black Housing

MODEL NUMBER: TLP310USBC



Clamps safely to your workstation to safeguard your computer, scanner and other electronics against surges, spikes and line noise, as well as charge mobile devices, including smartphones, tablets and MP3 players.

### Description

The TLP310USBC Protect It!® 3-Outlet Surge Protector features three NEMA 5-15R outlets and a surge suppression rating of 510 joules to protect your components against surges, spikes and EMI/RFI line noise that can damage sensitive electronics and destroy data. Plus, two USB ports produce 3.1A of combined power to charge your mobile devices, such as smartphones, tablets and MP3 players. Recommended for home, office, workstations, dorms and hotel rooms, the TLP310USBC mounts permanently to a clamp that attaches to most desks, tables and flat surfaces. The 10-foot (3.1-meter) power cord fits through the back of the clamp to reduce cable clutter. A top storage shelf holds smartphones and other small devices while they're charging.

### Features

#### Powers and Protects Electronic Components

- 3 NEMA 5-15R outlets accept most computers and peripherals
- 510 joules of surge suppression protect against surges, spikes and EMI/RFI line noise
- Recommended for home, office, workstations, dorms and hotel rooms

#### Powers and Charges Mobile Devices

- 2 USB ports (3.1A total) charge smartphones, tablets and other devices
- Top storage shelf accommodates smaller mobile devices during charging

#### Clamps Safely to Most Flat Surfaces

- Attaches permanently to adjustable clamp that fits most desks, tables and workstations
- Clamp adjusts from .59 to 1.77"
- 10 ft. AC power cord fits through back of clamp to avoid cable clutter

#### \$20,000 Ultimate Lifetime Insurance

- We will repair or replace any connected equipment damaged by surges up to \$20,000 for life
- Valid in the U.S., Canada and Puerto Rico only

### Highlights

- Clamp attaches firmly to most desks, tables and flat surfaces. Clamp adjusts from .59 to 1.77"
- 3 NEMA 5-15R outlets and 2 USB charging ports (3.1A total)
- 510 joules of surge suppression
- 10 ft. power cord reaches distant AC outlets

### Package Includes

- TLP310USBC Protect It! 3-Outlet Surge Protector
- Desk clamp
- Mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332198464
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Strip
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	X1 GREEN LED - PROTECTED
CHARGING	
Number of Charging Ports	2
Total Charging Watts	15.5
Charging Method	USB



Powering Business Worldwide



Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 3.1A
Overcharge Protection	No
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	510
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	1000
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	Black
Included Mounting Accessories	Mounting hardware
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	8.20 x 4.30 x 5.20
Shipping Dimensions (hwd / cm)	20.83 x 10.92 x 13.21
Shipping Weight (lbs.)	2.60
Shipping Weight (kg)	1.18
Unit Dimensions (hwd / in.)	1.940 x 1.760 x 5.510
Unit Dimensions (hwd / cm)	4.93 x 4.47 x 14.7
Unit Weight (lbs.)	2.34
Unit Weight (kg)	1.06
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No



Powering Business Worldwide



STANDARDS & COMPLIANCE	
Product Certifications	UL 1449; UL 962A
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.